



PCT-0200-050-OR-100

E1517959

Cable Tie, 200x4.8mm, Orange Plastic Barb



Product Properties:

|                                                                    |                   |
|--------------------------------------------------------------------|-------------------|
| Detectable                                                         | No                |
| Min. tensile strength                                              | 220 N             |
| Model                                                              | Internal toothing |
| Material quality                                                   | Polyamide (PA)    |
| Operating temperature                                              | -40-85 °C         |
| Band closure                                                       | Plastic lip/-cam  |
| UV-stable acc. ASTM D6779                                          | No                |
| Transparent                                                        | No                |
| Fluorescent                                                        | No                |
| Solvable fastener                                                  | No                |
| Text strip                                                         | None              |
| Type of fastening                                                  | None              |
| Colour                                                             | Orange            |
| Surface protection                                                 | Untreated         |
| Material                                                           | Plastic           |
| Halogen free                                                       | Yes               |
| Max. tensile force                                                 | 220 N             |
| Inflammability class of insulation material according to with UL94 | V2                |

Dimensions:

|                 |         |
|-----------------|---------|
| Bundle diameter | 2-54 mm |
| MOQ             | 100 .   |

|                      |        |
|----------------------|--------|
| Unit                 | pcs    |
| Length belt/tape/tie | 200 mm |
| Band width           | 4.8 mm |
| Max. tensile force   | 220 N  |

**Approvals:**

|                                                                    |     |
|--------------------------------------------------------------------|-----|
| Approved according to UR                                           | Yes |
| UL approval                                                        | Yes |
| Approved according to CE                                           | Yes |
| Inflammability class of insulation material according to with UL94 | V2  |

**Compliance:**

|                         |                                    |
|-------------------------|------------------------------------|
| CA Proposition 65       | In compliance                      |
| Conflict Minerals       | N/A, Contains no conflict minerals |
| Iron and Steel Sanction | Compliance                         |
| PFAS                    | No PFAS                            |
| PFOA                    | No PFOA                            |
| PFOS                    | No PFOS                            |
| POPs                    | No POPs                            |
| REACH                   | No SVHC (247 Subs. 21 Jan 2025)    |
| REACH Annex XIV         | No REACH Annex XIV                 |
| REACH Annex XVII        | No REACH Annex XVII                |
| RoHS                    | RoHS 3 (2015/863)                  |
| SCIP                    | Not Applicable                     |
| US TSCA                 | No (5 PBT Subs, Feb 2021)          |
| ECCN (EU)               | No CLASS                           |
| ECCN (US)               | EAR99                              |

**Other information:**

|                    |                      |
|--------------------|----------------------|
| ETIM-Class         | EC000046 - Cable tie |
| ETIM-Release       | 10.0                 |
| Trademark          | NEMIQ                |
| Product Group      | Cable ties, PCT & CT |
| Search Description | EVK2024              |
| Alternative SKU    | PCT-0200-050-OR-100  |
| E-no               | E1517959             |

**Logistic information:**

|                   |                                                                      |
|-------------------|----------------------------------------------------------------------|
| Barcode           | 733117640076                                                         |
| Country of origin | CN                                                                   |
| E-no              | E1517959                                                             |
| Item status       | Stock item, normally in stock with reservation for in between sales. |

|            |                     |
|------------|---------------------|
| MOQ        | 100 .               |
| Stock code | PCT-0200-050-OR-100 |
| Taric code | 39269097            |
| Unit       | pcs                 |

\*We reserve the right to make technical changes and disclaim any typographical errors.