


- 1- Pattes de fixations retractables / Retractable fixing lugs / Einziehbare Befestigungslaschen / Orecchioni di fissaggio retrattili / Patas de fijaciones retractables / Patilhas de fixação retrácteis
- 2- Borniers à vis d'alimentation / Screw power supply terminal blocks / Spannungsversorgung klemmenblock / Morsettiere a viti di alimentazione / Terminales de tornillos de alimentación / Terminais de parafusos alimentação
- 3- Afficheur LCD / LCD display / LCD-Anzeige / Afficheur LCD / Visualizzatore LCD / Pantalla LCD / Visor LCD
- 4- Borniers à vis des entrées / Inputs screw terminal blocks / Schraubklemmenblock / Morsettiere a viti delle entrate / Terminales de tornillos de las entradas / Terminais de parafusos das entradas
- 5- Touche de suppression / Delete key / Löschtaste / Tasto di soppressione / Tecla de supresión / Tecla de supressão
- 6- Touche insertion ligne / Insert line key / Taste zum Einfügen einer Zeile / Tasto inserimento linea / Tecla de inserción de línea / Tecla inserção linha
- 7- Touches de navigations ou après configuration boutons poussoir Z / Navigation keys or Z pushbutton keys after configuration / Tasten zum navigieren oder nach dem konfigurieren Drucktasten Z / Tasti di navigazione o dopo configurazione pulsanti Z / Teclas de navegación o después de configuración de botones pulsador Z / Teclas de navegação ou após configuração botões Z
- 8- Touche de selection / Selection key / Wahlteste / Tasto di selezione / Tecla de selección / Tecla de selección
- 9- Touche échappement / Escape key / Escape-Taste / Tasto escape / Tecla de escape / Tecla de escape
- 10- Emplacement cartouche EEPROM ou câble de raccordement PC / EEPROM cartridge or PC connection cable housing / Einbauplatz für EEPROM oder Anschlußkabel / Ubicazione cartuccia EEPROM o cavo di collegamento / Emplazamiento del cartucho EEPROM o cable de conexión / Posição cartucho EEPROM ou cabo de ligação
- 11- Borniers sorties relais / Relay outputs terminal blocks / Klemmenblöcke für Relaisausgänge / Morsettiere uscite relé / Terminales de salidas de relés / Terminais saídas relés
- 12- Emplacement pour étiquette relégendable / Zone for rewritable label / Stelle für mehrfach beschriftbares Etikett / Posto per etichetta con possibilità di aggiunta di legenda / Emplazamiento para etiqueta que puede llevar una nueva leyenda / Lugar para etiqueta reinscritivel.




Utiliser uniquement le câble spécifique SR1CBL01
 Use special cable SR1CBL01 only
 Ausschließlich das spezielle Kabel SR1CBL01 verwenden
 Utilizzare soltanto il cavo specifico SR1CBL01
 Utilizar únicamente el cable específico SR1CBL01
 Utilizar unicamente o cabo específico SR1CBL01


SR1-A101BD




SR1-A201BD




SR1-B121BD




SR1-B201BD






SR1-●101FU





SR1-●201FU




	SR1-●●●1FU	SR1-●●●1BD
a	72 mm	126 mm



> 7.5 mm (0.30 in.)




M4 x 20




mm ²	0.14...1.5	0.14...0.75	0.14...2.5	0.14...2.5	0.14...1.5
AWG	26...16	26...18	26...14	26...14	26...16
	C				
	Nm				
pound-inche					0.6
					5.4

SR1-●1●1BD



SR1-●201BD




1- Fusible ultra rapide 1A ou coupe circuit / 1A quick-blowing fuse or circuit-breaker / Ultraschnellsicherung 1A oder Geräteschutzsicherung / Fusibile ultra rapido 1A o interruttore / Fusible ultra rápido 1A o interruptor de circuito / Fusível ultra-rápido 1A ou corta-circuito
 3 - Charge résistive / Resistive load / Ohmsche Belastung / Carico resistivo / Carga de resistencia / Carga resistiva.


2- Fusible ou coupe circuit / Fuse or circuit-breaker / Ultraschnellsicherung oder Geräteschutzsicherung / Fusibile o interruttore / Fusible o interruptor de circuito

4 - Charge inductive / Inductive load / inductive Last / Carico induttivo / Carga inductiva / Charge Carga indutiva.

SR1-●101FU





SR1-●201FU





Possible uniquement sur les produits SR1-●●●1BD
 Only possible on SR1-●●●1BD products
 Nur bei den Produkte SR1-●●●1BD
 Possibile soltanto sui prodotti SR1-●●●1BD
 Possible unicamente en los productos SR1-●●●1BD
 Possivel unicamente nos produtos SR1-●●●1BD



Possible uniquement sur les produits SR1-B●●1BD
 Only possible on SR1-B●●1BD products
 Nur bei den Produkte SR1-B●●1BD
 Possibile soltanto sui prodotti SR1-B●●1BD
 Possible unicamente en los productos SR1-B●●1BD
 Possivel unicamente nos produtos SR1-B●●1BD

SR1-B121BD

SR1-B201BD

