



Double-ended ring spanners StahlwilleSTABIL®, imperial, deeply cranked

StahlwilleSTABIL® 20a

Product no. **41443436**
GTIN **4018754022458**
Model **20a 9/16 x 5/8**



Label. Double-ended ring spanner Size 9/16 x 5/8 " L.245mm

- Properties.**
- **imperial, differing** end sizes
 - deeply cranked
 - bi-hex with AS-Drive profile
 - durable, slim and lightweight design
 - high flexural strength due to double-T profile
 - STAHLWILLE's rounded finish ensures a non-slip, pleasant feel
 - drop-forged, hardened, and cooled in an oil bath
 - Chrome Alloy Steel, chrome-plated

Benefits.

High quality double-ended ring spanner, deeply cranked, in imperial AF spanner sizes.

Technologies and features.



Anti-Slip-Drive


The special AS-Drive profile makes high force transmission to the flats of bolts and nuts possible without damaging them. This also prevents stripping of the screw head.



Thin-walled rings

The thin-walled diameter of our rings makes it easier to work in confined spaces. The ring wall is deeper than standard nuts, which prevents jamming.

Technical drawing.



Technical attributes.

a1	10 mm
a2	12 mm
Drive profile	bi-hex AS-Drive
d1	21,3 mm
d2	25,3 mm
Length mm (L)	245 mm
Alloy	Chrome Alloy Steel
Surface	chrome-plated
Ring position	75 °
Size 1 [inch]	9/16 "
Size 2 [inch]	5/8 "
t	27 mm

Logistics data.

Depth mm (IFS)	255
Width mm (IFS)	26
Height mm (IFS)	30
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	265
Width (packaged, mm)	80
Height (packaging, mm)	55
Volume (packaged, dm3)	1.166 dm3
Product no.	41443436
Weight (gross, kg)	1,680
Weight PAP (kg)	0,000
Weight PVC (kg)	0,013
GTIN	4018754022458
Country of origin AWR	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82041100
Packing standard	10
Weight (g)	168 g

Variants.

Product no.	Model No. (ERP)	Description	GTIN
41441620	20a 1/4 x 5/16	Double-ended ring spanner Size 1/4 x 5/16 " L.180mm	4018754022410
41442428	20a 3/8 x 7/16	Double-ended ring spanner Size 3/8 x 7/16 " L.200mm	4018754022427
41443234	20a 1/2 x 9/16	Double-ended ring spanner Size 1/2 x 9/16 " L.220mm	4018754022441
41443436	20a 9/16 x 5/8	Double-ended ring spanner Size 9/16 x 5/8 " L.245mm	4018754022458
41443538	20a 19/32 x 11/16	Double-ended ring spanner Size 19/32 " L.255mm	4018754022465
41443640	20a 5/8 x 3/4	Double-ended ring spanner Size 5/8 x 3/4 " L.270mm	4018754022489
41443842	20a 11/16 x 13/16	Double-ended ring spanner Size 11/16 x 13/16 " L.300mm	4018754022502
41444044	20a 3/4 x 7/8	Double-ended ring spanner Size 3/4 x 7/8 " L.300mm	4018754022519
41444142	20a 25/32 x 13/16	Double-ended ring spanner Size 25/32 x 13/16 " L.300mm	4018754022526
41444446	20a 7/8 x 15/16	Double-ended ring spanner Size 7/8 x 15/16 " L.330mm	4018754022540
41444648	20a 15/16 x 1	Double-ended ring spanner Size 15/16 x 1 " L.330mm	4018754022557
41445258	20a 1 1/8 x 1 5/16	Double-ended ring spanner Size 1 1/8 x 1 5/16 " L.365mm	4018754022588

GTIN.



STAHLWILLE Eduard Wille GmbH

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal