

# Female test connector - PSBJ-URTK 6 YE



3026405

<https://www.phoenixcontact.com/gb/products/3026405>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

---

Female test connector, color: yellow



---

## Your advantages

- The test socket PSBJ... is used in place of the normal bridge screw and ensures the voltage pick-off on a bridged group of terminals
- The test sockets are tailored to the special applications encountered in the power supply industry

# Female test connector - PSBJ-URTK 6 YE



3026405

<https://www.phoenixcontact.com/gb/products/3026405>

## Commercial Data

Item number	3026405
Packing unit	10 pc
Minimum order quantity	10 pc
Sales Key	BE1Z3X
Product Key	BE1Z3X
Catalog Page	Page 587 (C-1-2019)
GTIN	4017918351205
Weight per Piece (including packing)	2.5 g
Weight per Piece (excluding packing)	2.4 g
Customs tariff number	85366990
Country of origin	PL

# Female test connector - PSBJ-URTK 6 YE



3026405


<https://www.phoenixcontact.com/gb/products/3026405>

## Technical Data

### Product properties

Product type	Test socket
Number of positions	1

### Dimensions

Dimensional drawing	
Width	6 mm
Height NS 35/7,5	15 mm
Length	6 mm
Pin diameter	4.1 mm

### Material specifications

Color	yellow
Material	Brass
Insulating material	PA

### Connector

Number of positions	1
Connection method	Screw connection
Material	Brass
Number of positions	1
Connection method	Screw connection
Material	Brass

### Environmental and real-life conditions

#### Ambient conditions


Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

# Female test connector - PSBJ-URTK 6 YE

3026405

<https://www.phoenixcontact.com/gb/products/3026405>

## Drawings



# Female test connector - PSBJ-URTK 6 YE



3026405

<https://www.phoenixcontact.com/gb/products/3026405>

## Classifications

### ECLASS

ECLASS-9.0	27440313
ECLASS-10.0.1	27440313
ECLASS-11.0	27440313

### ETIM

ETIM 8.0	EC002255
----------	----------

### UNSPSC

UNSPSC 21.0	20122000
-------------	----------

# Female test connector - PSBJ-URTK 6 YE



3026405

<https://www.phoenixcontact.com/gb/products/3026405>

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Phoenix Contact 2022 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)