



SIMATIC WinCC RC software upgrade from V7.3/7.4 to V8.0 for SIMATIC WinCC Runtime & Configuration (RC), including options Redundancy, Server, User Archive, Web Navigator, Web NAV Load-Balancing, Web Diagnostics Client/Server, Data Monitor, Connectivity Pack, Connectivity Station runtime/configuration software on DVD, single license, license key on USB flash drive -- content: set (3x DVD + 1x USB)

| Operator control and monitoring                |         |
|------------------------------------------------|---------|
| Object block library                           | Yes     |
| Alarm system (incl. buffer and acknowledgment) | Yes     |
| Report system/log system                       | Yes     |
| SQL database                                   | Yes     |
| Process diagnostics                            | No      |
| SCADA functionality                            | Yes     |
| Sector-specific and technological expansions   | Yes     |
| User archive/recipe management                 | Yes     |
| Interfaces                                     |         |
| Programming interfaces                         | Yes     |
| OPC-DA interface, Server                       | Yes     |
| OPC-DA interface, Client                       | Yes     |
| Hardware requirement                           |         |
| Processor                                      |         |
| • Processor cycle frequency, min.              | 2.5 GHz |
| Memory                                         |         |
| • Main memory, min.                            | 4 Gbyte |
| Operating systems                              |         |
| Runs under operating system                    |         |
| • Windows 2000                                 | No      |
| • Windows 2003 Server                          | No      |
| • Windows Vista                                | No      |
| • Windows XP                                   | No      |
| • Windows 7                                    | No      |
| • Windows 8                                    | No      |
| • Windows 10                                   | Yes     |
| Configuration                                  |         |
| Online configuration                           | Yes     |
| Number of multi-user configurations, max.      | 32      |
| Script languages (Runtime)                     |         |
| • Number of Visual Basic Scripts               | Yes     |
| • other                                        | Yes     |
| Know-how protection                            |         |
| • Password protection                          | Yes     |
| Languages                                      |         |
| Configuration languages                        |         |
| • Number of configuration languages            | 70      |
| Classifications                                |         |

|        | Version | Classification |
|--------|---------|----------------|
| eClass | 14      | 27-24-25-02    |
| eClass | 12      | 27-24-25-02    |
| eClass | 9.1     | 27-24-25-02    |
| eClass | 9       | 27-24-25-02    |
| eClass | 8       | 27-24-25-02    |
| eClass | 7.1     | 27-24-25-02    |
| eClass | 6       | 27-24-25-02    |
| ETIM   | 10      | EC001416       |
| ETIM   | 9       | EC001416       |
| ETIM   | 8       | EC001416       |
| ETIM   | 7       | EC001416       |

last modified:

2/6/2024 