

P391 - EAGLE FFP3 Valved Dolomite Fold Flat Respirator (Pk10)

Collection: Disposable Mask FFP3

Range: Disposable Masks

Materials: PP, Mesh with PU Foam

Inner Pack: 10

Outer Carton: 16

Product information

Innovative compact folding mask with 7 dynamic parts providing excellent facial movement with maximum comfort. Valved and with inner foam to increase the comfort of the wearer. DOLOMITE optional clogging test. An individual polybag and special flat shape make it easy to store and vending machine ready.



Disposable Mask FFP3

Disposable mask FFP3 level, protects against solid and liquid particles of high toxicity. Minimal % of filtration 99%. Protects up to 20 times the TLV (Assigned Protection Factor for FFP3 masks) or up to 50 times TLV (Nominal Protection Factor for FFP3 masks). Examples of applications: Sanding of hard wood (beech, oak) / treatment of wood using copper, chrome or arsenic based products / impact stripping of paint / sanding of cement. Exceptional quality and performance are ensured across our range of disposable masks.

Disposable Masks

Our Biztex® brand ensures exceptional quality and performance across our full range of disposable masks. The extensive Biztex® range offers a high level of protection and quality safeguarding the wearer against many workplace risks including liquid chemicals, static electricity, dry particles and radioactive contamination. The complete Biztex® range includes disposable masks and limited-life garments.

Standards

EN 149:2001 +A1:2009 FFP3 (NR D)

Features

- 7 ergonomic points which adapt to different face shapes
- High performance exhalation valve to reduce heat and provide comfort when used in hot and humid conditions
- Flexible shape which allows the mask to be folded flat
- Individually wrapped inside hygienic polybag
- Adjustable nose bar for improved fit and reduced fogging of glasses
- Foam padding around the nose bridge for additional comfort
- Dolomite optional clogging test (D) to provide more comfortable breathing and longer lasting filtration performance
- Retail box which aids presentation for retail sales
- Individually packed for vending machines
- CE certified
- UKCA marked



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

P391 - EAGLE FFP3 Valved Dolomite Fold Flat Respirator (Pk10) **Commodity Code: 6307909311**

Test House

BSI Group The Netherlands B.V. (Notified Body No.: NB: 2797)
John M. Keynesplein 9
, The Netherlands
Cert No: CE 758390

BSI Assurance UK Ltd (Notified Body No.: AB: 0086)
The British Standards Institution
MK5 8PP, United Kingdom
Cert No: UKCA 744166

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
P391WHR	White	52.0	43.0	49.0	0.1750	0.1096	5036108273690	25036108763799