

Grip-Fit & Grip-Fit Plus

Supported Rubber Gloves

Ref. No. L485, L486, L585, L586, L685, L686

Intermediate Design

Description

Sanitized®

Dipped 100% Natural Rubber Industrial Gloves on a 100% cotton liner with a tough yet very flexible "crinkle" finish coating and elasticated knitted wrist. The gloves offer excellent levels of comfort, flexibility and sensitivity, this significantly reduces hand fatigue where gloves are worn over long periods. The "crinkle" finish gives outstanding wet and dry grip along with good cut resistance, with a reinforced grip for handling glass and sheet metal. The glove is made on a anatomically designed handshape which allows the glove to mould to the contours of the hand for an outstanding fit.

Applications:

Light Duty (Grip-Fit), Heavy Duty (Grip-Fit Plus) mechanical protection

Both of these gloves offer a level of comfort not normally associated with mechanical handling gloves.


GRIP-FIT is an ideal dry handling general purpose glove with excellent dexterity, comfort and flexibility.

GRIP-FIT PLUS with a brushed jersey liner gives extra insulation in outdoor conditions and added cushioning protection against knocks and scrapes.


Ideal for use in the glass, plastics, tile, ceramics, tin plate and sheet metal industries. Suitable for handling bricks, timber, concrete blocks, veneers, and refuse collection etc.



L586



L485



Certificate No. SO79 /9 2

GRIP-FIT


Grip-Fit & Grip-Fit Plus

Natural Rubber Industrial Gloves Intermediate Design (Category 2)

Reference No.	Description	Sizes (EN Size)
Grip-Fit Lightweight		
L485	Orange palm coated Knitwrist interlock liner	7, 8, 9, 10
L486	Orange fully coated Knitwrist interlock liner	7, 8, 9, 10
Grip-Fit Plus Heavyweight		
L585 Grip-Fit Plus	Blue palm coated Knitwrist interlock liner	7, 8, 9, 10
L586 Grip-Fit Plus	Blue fully coated Knitwrist interlock liner	7, 8, 9, 10
L685 Grip-Fit Plus	Blue palm coated Knitwrist Jersey liner	8, 9, 10
L686 Grip-Fit Plus	Blue fully coated Knitwrist Jersey liner	8, 9, 10

Materials

Dipped Natural Rubber gloves on 100% cotton liners for handling sharp and slippery materials with a high level of comfort, dexterity and flexibility.



CE EN 388:1994


Protective glove
against mechanical
risks.

Abrasion
Blade cut
Tear
Puncture


Performance test results

	GRIP-FIT	GRIP-FIT PLUS
Abrasion	Level 3	Level 4
Blade cut	Level 1	Level 1
Tear	Level 2	Level 4
Puncture	Level 1	Level 1

Area of protection



L485, L585, L685



L486, L586, L686

GRIP-FIT

*"Hands on
Protection"*



**John Ward & Sons
(Stourbridge) Ltd.**

P.O. Box 12
Gainsborough Trading
Estate, Rufford Road,
Stourbridge,
West Midlands.DY9 7NB.

United Kingdom.

Tel: 01384 374284

Fax: 01384 378792

Due to the nature of these products the dimensions and performance figures expressed are average values. If used in accordance with the information supplied the gloves will have a long service life. This is dependent on the overall treatment and application of the gloves. These gloves will not provide full protection if they are damaged, used incorrectly, or used in conditions more severe than those on this notice or other John Ward and Sons literature.