

Datasheet

RS PRO MCT is a crimp tool frame for mobile tool easily interchangeable crimp dies.

Stock No: 492-9595



Features & Benefits:

- Crimp dies are kept together with a special pin to simplify handling.
- Reliable – crimping performance is consistent and accurate with a parallel action stroke.
- Easy to use – designed to give the user full visibility of the crimping process. Handles are shaped for low effort crimping with a one or two hand grip.
- Versatile – an easy-access release function allows fast and simple exchange of crimp dies. No special tools needed.
- Weight and size of the tool are optimized to make it easy to carry. Dies are kept in pairs and delivered in a modular reusable box.
- Hole in handle allows attachment of safety strap

TECHNICAL DATA

Length: 234 mm/9.21"

Width: 31 mm/1.22"

Height: 64 mm/2.52"

Weight: 460 gr/1.23 lb

Description: Tool frame for mobile die sets.

Life span, cycles: 20,000

Available die sets

- 458-402 MCT Die set RG213/RG214
- 458-412 MCT die set BT 2002/2003
- 458-418 Die Set for Yellow sealed splices
- 458-424 Die Set for Blue/red sealed splices
- 492-9618 DIE INSL 4-6/0,1-0.4 MM²,12-10/26-22AWG
- 492-9624 Insulated Die Set,1.5-2.5,0.5-1.5mm sq.
- 492-9630 Uninsulated Termnl Die Set,0.75-2.5mm sq
- 492-9646 Uninsulated Terminal Die Set,4-10mm sq.
- 492-9652 Ferrules Die Set,0.25-10mm sq.
- 492-9668 Die Set,F Style,2.8/110,0.1-1.0mm sq.
- 492-9674 Die Set,F style,4.8/187 0.5-2.5mm sq.
- 492-9680 Die Set,Fstyle,6.3/250 0.5-6.0mm sq.
- 492-9703 Die set,Coax,RG174/179,BNC,Hex,
- 492-9719 Die set,coax,RG58/59/62/71 BNC/TNC Hex
- 492-9725 Data plug,RJ45, 8/8
- 492-9731 Die set,RJ11 for 6/6,6/4 & 6/2
- 548-3185 FERRULE DIE 16+25MM
- 548-3191 FERRULE DIE 35+ 50MM
- 548-3208 COAX CATV RG6 59 DIE
- 548-3214 TURN PIN DIE 0.14-4MM
- 683-1658 MCT Die for Flag terminals
- 698-7811 Die for open barrel MC3 PV
- 698-7815 Die for turned pin solar lok PV
- 698-7818 Die for Turned pin MC4 PV
- 810-0723 Die set with wire seal crimp, 0.5-6mm
- 810-0732 Die set with wrap around crimp,0.5-6mm
- 810-0735 Die set with over-lap crimp,0.5-6mm
- 810-0741 MCD Timer connectors-wireseal
- 810-0745 MCD Timer connectors-no seal
- 810-0754 MCD 1.5system-wire seal

