



1510

Protector

Carry-On Case

The original case introduced over 45 years ago has since evolved into the global standard for equipment protection. The Protector Case series is designed to survive and trusted to travel to the harshest environments on earth.

The Peli 1510 Protector Case provides military-grade protection for a wide variety of gear, from camera equipment to camping kits. It is available with foam, without foam, padded dividers, or TrekPak dividers. The Peli 1510 Protector Case is the maximum airline carry-on size, so you can travel with your sensitive gear close at hand.

(Check with your airline for exact measurement requirements)

- Watertight, crushproof, and dustproof construction for total protection in any environment
- Cabin friendly design suitable for carry on travel on many airlines, subject to individual airline policies*
- O-ring seal
- Customizable interior options including foam, padded dividers, or TrekPak dividers
- Precision foam customization available for a perfect fit around your equipment
- Case personalization with vinyls for names, logos, or custom graphics
- Bold color options including pink, yellow, black, orange and more
- Automatic pressure equalization valve - balances interior pressure, keeps water out
- Peli™ Limited Lifetime Guarantee**



CONFIGURATIONS



DIMENSIONS

Interior (L×W×D)	19.75 x 11.00" x 7.60 (50.2 x 27.9 x 19.3 cm)
Exterior (L×W×D)	22.00 x 13.81" x 9.00 (55.9 x 35.1 x 22.9 cm)
Lid Depth	1.79" (4.5 cm)
Bottom Depth	5.79" (14.7 cm)
Total Depth	7.58" (19.3 cm)
Int Volume	0.96 ft ³ (0.027 m ³)
Padlock Hole Diameter	0.31" (0.8 cm)

MATERIALS

Body	Polypropylene
Latch	ABS
O-Ring	Polymer
Pins	Stainless Steel
Foam	1.3 lb Polyurethane

Purge Body
Purge Vent

ABS
3 Micron Hydrophobic Non-Woven

COLOURS

Black
Pink

Desert Tan

Orange

Yellow

WEIGHT

Weight With Foam	13.60 lbs (6.17 kg)
Weight Empty	11.99 lbs (5.44 kg)
Buoyancy	64.15 lbs (29.1 kg)
Weight With TrekPak / Foam Hybrid	14.94 lbs (6.78 kg)
Master Pack Weight	32.43 lbs (14.71 kg)

TEMPERATURE

Minimum Temperature	-40°F (-40 °C)
Maximum Temperature	190°F (87.8 °C)

CERTIFICATIONS

IP67
Def Stan 81-41

OTHER

Wheels	2
Extendable Handle	yes
Master Pack	2
Nameplate	yes
Reduced Area	yes
Military	yes

ACCESSORIES



1511
4 pc. Replacement Foam Set



1513
Replacement O-ring



1515
Padded Divider Set



1519
Lid Organizer



1510EUTP
TrekPak Case Divider Kit



1510TPKIT
TrekPak Case Divider Kit




1510TPDIV
Extra TrekPak Dividers



1507QM
Quick Mounts - set of 4



1506TSA
TSA Lock



1500D
Desiccant Silica Gel



1510MP
EZ-Click™ MOLLE Panel



RucPac-Pro-1
RucPac Pro Hardcase
Backpack Conversion



RucPac-normal
RucPac Standard Hardcase
Backpack Conversion

Peli

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999
info@peli.com • www.peli.com

Document created on 08-19-26