

Top Dog Manufacturing

26 Linkletter Avenue
Summerside, PE
Canada C1N 4J9

TEL 902-887-3063
TOLL FREE 1-800-472-2412
EMAIL topdog@topdogmfg.com

**TECHNICAL DATA SHEET**

Gown

**Product Information****Reusable****Care Instructions****Liquid proof barrier****Compliance****Colours****Anti-microbial Thickness****Sizing Chemical Resistance****Wearability****Full frontal protection with open back for breathability.**

A popular choice when more protection than an apron / sleeve combo is required. The overhead design and elastic cuff make the gown extremely easy to don and doff. Lightweight, protective, and comfortable.

100% Pure Polyurethane (PU) Ether.

Industry leading durability.

PU material will never crack.

Reusable: Day after day, week after week, month after month. **Top Dog products last longer.**

Launderable: Dip wash and hang dry (**Pure PU absorbs zero moisture**).

Machine washable and laundry safe to 82°C (180°F): Refer to laundering / cleaning instructions.

Liquid proof barrier.

100% recyclable.

Food safe.

CFIA, FDA/USDA and EU compliant.

Industry leading 6 colour choices. Aligns with colour coding and HACCP initiatives.

Enhanced anti-microbial properties: Mold will not grow on this material.

Thickness of 6 and 8mil (150 and 200 microns) available.

8mil [200 microns] designed for heavy duty applications.

Length of 56" (142cm).

Custom sizing available.

15 mil (300 Microns) belly patch available.

100% resistant to animal fats, degreasers, cleaning chemicals and water (plus many more fluids and chemicals): Contact Top Dog for details regarding chemical compatibility.

Soft / supple to -65°C.

Lightweight, supple and comfortable to wear.

Pure PU is slick: Virtually zero abrasion or adhesion; almost nothing sticks to (or stains) PU (grease, food/processing waste, glue, etc.).

The best choice in protective apparel – See page 2 for product numbers

Gown Product Numbers



(Add a "B" at the end of the product number if you are requesting bulk packaging. Bulk packed items are not individually bagged).

Thickness	Colour	Size	Product Number	Case Quantity
6 mil	Dark Blue	Large	101.0100	10
6 mil	Royal Blue	Large	101.0104	10
6 mil	White	Large	101.0101	10
6 mil	Yellow	Large	101.0102	10
6 mil	Red	Large	101.0105	10
6 mil	Green	Large	101.0107	10
6 mil	Dark Blue	X-Large	101.0200	10
6 mil	Royal Blue	X-Large	101.0204	10
6 mil	White	X-Large	101.0201	10
6 mil	Yellow	X-Large	101.0202	10
6 mil	Red	X-Large	101.0206	10
6 mil	Green	X-Large	101.0207	10
6 mil	Dark Blue	2X-Large	101.0300	10
6 mil	Royal Blue	2X-Large	101.0304	10
6 mil	White	2X-Large	101.0301	10
6 mil	Yellow	2X-Large	101.0302	10
6 mil	Red	2X-Large	101.0306	10
6 mil	Green	2X-Large	101.0307	10
6 mil	Dark Blue	3X-Large	101.0400	10
6 mil	Royal Blue	3X-Large	101.0123	10
6 mil	White	3X-Large	101.0401	10
6 mil	Yellow	3X-Large	101.0402	10
6 mil	Red	3X-Large	101.0406	10
6 mil	Green	3X-Large	101.0407	10
8 mil	Dark Blue	Large	101.1100	10
8 mil	Royal Blue	Large	101.1104	10
8 mil	White	Large	101.1101	10
8 mil	Yellow	Large	101.1102	10
8 mil	Red	Large	101.1105	10
8 mil	Green	Large	101.1405	10
8 mil	Dark Blue	X-Large	101.1200	10
8 mil	Royal Blue	X-Large	101.1204	10
8 mil	White	X-Large	101.1201	10
8 mil	Yellow	X-Large	101.1202	10
8 mil	Red	X-Large	101.1205	10
8 mil	Green	X-Large	101.1505	10
8 mil	Dark Blue	2X-Large	101.1300	10
8 mil	Royal Blue	2X-Large	101.1304	10
8 mil	White	2X-Large	101.1301	10
8 mil	Yellow	2X-Large	101.1302	10
8 mil	Red	2X-Large	101.1305	10
8 mil	Green	2X-Large	101.1705	10
8 mil	Dark Blue	3X-Large	101.1400	10
8 mil	Royal Blue	3X-Large	101.1123	10
8 mil	White	3X-Large	101.1401	10
8 mil	Yellow	3X-Large	101.1402	10
8 mil	Red	3X-Large	101.1406	10
8 mil	Green	3X-Large	101.1605	10