

E-RANGER

INNOVATIVE UNVENTED SAFETY HELMET WITH CRASHBOX IMPACT ABSORPTION SYSTEM



FEATURES

- › Crashbox - the patented, double walled impact absorption system located at the top of the helmet
- › Unvented
- › Patented oval shaped slots for attaching hearing or eye/face protection and head light
- › 6-point textile suspension harness
- › Ratchet - easy to adjust even with gloves on
- › Microfibre sweatband
- › 4-point self-releasing chin-strap mounts
- › Adjustable padded headband
- › IntegraSpec - retractable eye protection (optional)

SUITABLE APPLICATIONS

- › Electrical work

CERTIFICATION

- › CE
- › EN 397
- › EN 50365
- › Molten Metal MM

PRODUCT CODES

E-RANGER + Colour Code

EXAMPLE: White Helmet with White Crashbox

E-RANGER WH (WH C/Box)

COLOUR CODES		CRASHBOX							
		○	●	●*	●	●	●	●	●
HELMET	○	WH (WH C/Box)	WH (YE C/Box)	WH (HVO C/Box)	WH (RE C/Box)	WH (BL C/Box)	WH (GN C/Box)	WH (BK C/Box)	
	●	YE (WH C/Box)	YE (YE C/Box)	YE (HVO C/Box)	YE (RE C/Box)	YE (BL C/Box)	YE (GN C/Box)	YE (BK C/Box)	
	●*	HVO (WH C/Box)	HVO (YE C/Box)	HVO (HVO C/Box)	HVO (RE C/Box)	HVO (BL C/Box)	HVO (GN C/Box)	HVO (BK C/Box)	
	●	RE (WH C/Box)	RE (YE C/Box)	RE (HVO C/Box)	RE (RE C/Box)	RE (BL C/Box)	RE (GN C/Box)	RE (BK C/Box)	
	●	BL (WH C/Box)	BL (YE C/Box)	BL (HVO C/Box)	BL (RE C/Box)	BL (BL C/Box)	BL (GN C/Box)	BL (BK C/Box)	
	●	GN (WH C/Box)	GN (YE C/Box)	GN (HVO C/Box)	GN (RE C/Box)	GN (BL C/Box)	GN (GN C/Box)	GN (BK C/Box)	

* HI-VIZ

E-RANGER

TECHNICAL SPECIFICATIONS

TEMPERATURE RESISTANCE	Low temperature	-20°C (EN) -30°C (ANSI)
	High temperature	+50°C (EN)
SHELL MATERIAL	ABS/Polycarbonate Blend/UV blocker	
HARNESS MATERIAL	Polyester	
HEADBAND MATERIAL	Polyethylene	
SWEATBAND MATERIAL	Microfibre, PU	
SLOTS	30mm	
WEIGHT	375g	
FITTING SIZES	53-62cm	
IN-USE LIFETIME	Up to 6 years (if undamaged)	
ELECTRICAL INSULATION	440V AC (EN 397) 1000V AC / 1500V DC (EN 50365) 10000V disruptive discharge voltage (EN 50365)	

PACKAGING AND MAINTENANCE

CLEANING	Helmet can be hand washed and cleaned with warm soapy water. Chemicals or abrasive cleaners should not be used.
STORAGE	Storage out of direct sunlight in original packaging is recommended.
DISPOSAL	Disposal via normal waste; material is ideal for incineration. Material is not recycled and is not biodegradable.
PACKAGING	1 helmet / box • 6 boxes / case

CORPORATE BRANDING

- › Up to 4 colour logo printing
- › Maximum printing sizes - 50 x 28mm
- › Positioned on the front right
- › Other options available upon request

SPARE PARTS / ACCESSORIES Other accessories available on request

AREA	ITEM	ORDER CODE	
CHIN-STRAP	Chin-strap, textile band, 20mm, 4-point	9256 Chin-strap	
	Chin-strap, textile band, 20mm, fast-click ratchet, 4-point	9257 Chin-strap	
COMFORT	Harness with ratchet	2006LDRA Textile Harness	
	Microfibre sweatband	9228L	
EYE	IntegraSpec eye protection (32g)	Clear	Integra Spec Clear
		Tinted	Integra Spec Tinted
VISIBILITY	22 piece reflectors set	Sticker Set	

www.alphasolway.com **T: +44 (0)1461 202452** **E: sales@alphasolway.com**

ALPHA SOLWAY LTD, Factory 1, Queensberry Street, Annan, DG12 5BL, UK

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary. © 2018 Alpha Solway Ltd

ALPHA
SOLWAY