

## Features

- Flexible and durable H05VVF3G0.75- pvc cable
- European plug VII-Angled CEE (7)
- Moulded IEC -C13 Connector Striaight
- Fully moulded connectors for strength and durability
- Integrated strain relief for connection support and protection
- Universal C13 IEC connector

## RS PRO 2.00m Power cable C13, IEC to VII CEE (7) 10A 250 V

RS Stock No.: 0794491



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

- From RS PRO a high quality and durable power cord used for connecting an appliance to a mains power supply. This power cord is fully equipped with a European (VII) 2-Pin and Earth strip on one end and an IEC C13 type connector on the other that connects to the appliance. The power cord is fully moulded and features integrated strain reliefs that provide additional protection and support to the connectors, with a cable length of 2.00mtrs.

## General Specifications

|               |                                                                                                                                                                                                                                                                                                                                                                               |
|---------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Connector A   | C13, IEC Female – Straight EN60320 /C13                                                                                                                                                                                                                                                                                                                                       |
| Connector B   | CEE (7) VII Male – Angled                                                                                                                                                                                                                                                                                                                                                     |
| Sheath Colour | White                                                                                                                                                                                                                                                                                                                                                                         |
| Material      | PVC                                                                                                                                                                                                                                                                                                                                                                           |
| Applications  | DIY and home improvements, Maintenance work, Household Entertainment (TVs, Satellite boxes, routers etc.) Industrial machines and equipment Office desks (monitors, computers, phones) Any Electrical device needed to be connected by mains, Cassette recorders, Battery/mains operated radios, battery chargers, laptop computers, power supplies and video games consoles. |

## Mechanical Specifications

|        |       |
|--------|-------|
| Length | 2.00m |
|--------|-------|

## Electrical Specifications

|                            |                                              |
|----------------------------|----------------------------------------------|
| Power Cord Rating          | 10A - 250V                                   |
| Visual Inspection          | 100%                                         |
| Electrical Test            | 100%                                         |
| High pot test wire to wire | 3.000Vac for 2 sec.                          |
| Continuity test            | 25Aac to grounding / 20A to line and neutral |
| Polarity test              | yes                                          |
| Skin high pot test         | 6.000Vac line to skin                        |

## Protection Category


|                          |                                                        |
|--------------------------|--------------------------------------------------------|
| Environmental Conformity | Eu-Directive 2002/96/EC (WEEE)                         |
|                          | Eu-Directive 2003/11/EC (Council Directive 76/769/EEC) |
|                          | Eu-Directive 2002/95/EC (RoHS-Compliant)               |

## Approvals

|               |                                                  |
|---------------|--------------------------------------------------|
| C13 CONNECTOR | ENEC, CE                                         |
| VII CEE (7)   | VDE, OVE, CEBEC, KEMA, S, D, N, FI, LCIE, IMQ, K |
| Cable         | Harmonised <HAR>                                 |

All dimensions in mm

2000 +/- 50



All Dimensions in mm