



XAPG39400

Table 19.287: Undrilled Die Cast Enclosures (Painted Gray RAL7032)

Type	Material	Usable Depth		H x W x D Dimensions		Catalog Number	\$ Price
		IN	mm	IN	mm		
NEMA 4, 13	Zinc	1.93	49	3.15 x 3.15 x 2.03	80 x 80 x 51.5	XAPG19100	110.00
				5.12 x 3.15 x 2.03	130 x 80 x 51.5	XAPG29100	120.00
				6.89 x 3.15 x 2.03	175 x 80 x 51.5	XAPG39100	142.00
		2.93	74.5	3.15 x 3.15 x 3.03	80 x 80 x 77	XAPG19400	110.00
				5.12 x 3.15 x 3.03	130 x 80 x 77	XAPG29400	120.00
				6.89 x 3.15 x 3.03	175 x 80 x 77	XAPG39400	142.00
	Aluminum	2.93	2.93	8.66 x 3.15 x 3.03	220 x 80 x 77	XAPG49400	174.00
				12.20 x 3.35 x 3.03	310 x 85 x 77	XAPG59400	262.00

Table 19.288: Drilled Die Cast Enclosures (Painted Gray RAL7032) ▲

Type	Material	Usable Depth		Number of 22 mm holes	H x W x D Dimensions		Catalog Number	\$ Price
		IN	mm		IN	mm		
NEMA 4, 13 1.18 in. (30 mm) centerline spacing of holes for horizontal mount	Zinc	1.93	49	2	3.15 x 3.15 x 2.03	80 x 80 x 51.5	XAPG19702	120.00
				3	5.12 x 3.15 x 2.03	130 x 80 x 51.5	XAPG29703	142.00
				4	6.90 x 3.15 x 2.03	175 x 80 x 51.5	XAPG39704	174.00
		2.93	74.5	2	3.15 x 3.15 x 3.03	80 x 80 x 77	XAPG19802	120.00
				3	5.12 x 3.15 x 3.03	130 x 80 x 77	XAPG29803	142.00
				4	6.90 x 3.15 x 3.03	175 x 80 x 77	XAPG39804	174.00
NEMA 4, 13 1.58 in. (40 mm) centerline spacing of holes for vertical mount	Zinc	1.93	1.93	1	3.15 x 3.15 x 2.03	80 x 80 x 51.5	XAPG19201	110.00
				2	5.12 x 3.15 x 2.03	130 x 80 x 51.5	XAPG29202	120.00
				3	6.90 x 3.15 x 2.03	175 x 80 x 51.5	XAPG39203	142.00
		2.93	74.5	1	3.15 x 3.15 x 3.03	80 x 80 x 77	XAPG19501	110.00
				2	5.12 x 3.15 x 3.03	130 x 80 x 77	XAPG29502	120.00
				3	6.90 x 3.15 x 3.03	175 x 80 x 77	XAPG39503	142.00
	Aluminum	2.93	74.5	4	8.66 x 3.15 x 3.03	220 x 80 x 77	XAPG49504	174.00
				5	12.20 x 3.35 x 3.03	310 x 85 x 77	XAPG59505	268.00

▲ Can use either XB4 or XB5 products.

Table 19.289: Drilled Flush Plates ■

Type	Material	Number of 22 mm holes	H x W x D Dimensions		Catalog Number	\$ Price
			IN	mm		
NEMA 4, 13 1.18 in. (30 mm) centerline spacing of holes	Anodized Aluminum	1	2.83 x 2.83	72 x 72	XAPE301	52.00
		2	4.13 x 2.83	105 x 72	XAPE302	60.00
		3	5.43 x 2.83	138 x 72	XAPE303	68.00
		4	6.73 x 2.83	171 x 72	XAPE304	82.00
		5	8.03 x 2.83	204 x 72	XAPE305	98.00

■ Can use either XB4 or XB5 products.

Table 19.290: Optional Back Box (for finger protection, if required)

Type	Material	For Use With	Catalog Number	\$ Price
Protective rear covers	Insulating Fiberglass	Flush plate XAPE301	XAPE901	32.80
		Flush plate XAPE302	XAPE902	
		Flush plate XAPE303	XAPE903	
		Flush plate XAPE304	XAPE904	
		Flush plate XAPE305	XAPE905	60.00