

Universe	Professional
Type	Lighting
Category	Ultra-compact headlamps
Subcategory	Ultra-compact headlamps



hybrid
CONCEPT

TACTIKKA®


Designed for the workshop, small maintenance jobs, or concerts and shows, the TACTIKKA headlamp offers 300-lumen brightness and a flood beam for comfortable proximity lighting. It also has red lighting to ensure stealth. TACTIKKA comes with 3 standard batteries and is also compatible with the CORE rechargeable battery, thanks to the HYBRID CONCEPT design. Mounting accessories allow the lamp to be attached to any kind of helmet.



Uniform flood beam for comfortable close-range vision. White lighting, or red for nighttime stealth.



Compact headlamp.



HYBRID CONCEPT design: TACTIKKA comes with three standard batteries and is also compatible with the CORE rechargeable battery.

Short Description Compact headlamp with flood beam for proximity lighting. White lighting, or red to ensure nighttime stealth. 300 lumens

- Selling Points**
- Compact and lightweight: only 82 g
 - Easy to use:
 - three white brightness levels for comfortable proximity lighting
 - red lighting (continuous or strobe) combines visual comfort and stealth
 - single button for quick and easy selection of brightness or light color
 - ergonomic button, even with gloves
 - HYBRID CONCEPT design: TACTIKKA comes with three standard batteries and is also compatible with the CORE rechargeable battery
 - detachable, washable headband
 - compatible with mounting accessories that allow the lamp to be attached to any kind of helmet
 - Available in three colors, depending on use
-

- Specification**
- Brightness: 300 lumens (ANSI/PLATO FL 1)
 - Weight: 82g
 - Beam pattern: flood
 - Energy: Three AAA/LR03 batteries (included) or CORE rechargeable battery (available as accessory)
 - Battery compatibility: alkaline, lithium or Ni-MH rechargeable
 - Certification(s): CE
 - Watertightness: IPX4 (weather-resistant)
-

Lighting performance

Lighting performance as defined by the ANSI/PLATO FL 1 protocol					
Lighting color	Lighting levels	Brightness	Distance	Burn time	Reserve
white	proximity	6 lm	10 m	120 h	-
	movement	100 lm	40 m	9 h	30 h
	distance vision	300 lm	65 m	2 h	40 h
red	proximity	2 lm	5 m	60 h	-
	strobe	visible at 700 m for 400 h			

Specifications by reference

Reference(s)	E093HA00	E093HA01	E093HA02
			
Color(s)	black	camo	desert
Made in	MY	MY	MY
Guarantee	5 years	5 years	5 years
Packing	1	1	1
Case quantity	50	50	50
EAN	3342540827837	3342540827844	3342540827851

Accessory(ies) CORE
KIT ADAPT
FIXATION TACTIKKA®
SHELL L

Related product(s) VERTEX®
VERTEX® VENT
STRATO®
STRATO® VENT
Countertop or wall display for headlamps
Floor display for pro headlamps
Rotating floor display for pro headlamps