

AC/DC 24 V

10 A

AC 230 V or AC/DC 24 V

10 A

L1 – Q1 – Q2 – Q3

230 V on L1 ⇒ 230 V on Q1, Q2, Q3

24 V on L1 ⇒ 24 V on Q1, Q2, Q3

ON

OFF

1

2

3

4

5

6

7

8

DIP's:

ON =

OFF =

DIP No.: 1...8

DIP No.: 1...8

Application	V1	Outputs	
		DC	On/Off
① 2-pipe			

Application	V1	V2	Outputs			
			DC	DC	On/Off	On/Off
② 2-pipe with electric heater						
③ 2-pipe with radiator						
④ 4-pipe						
⑤ 2-pipe/2-stage						

Application	V1	V2	V3	V4	Outputs	
					DC	DC
⑥ 4-pipe with electric heater						
⑦ 4-pipe/2-stage						

Application	V1	V2	Outputs	
			DC ()	DC (PICV) On/Off
⑧ 4-pipe with 6-port ball valve				
⑩ 4-pipe with 6-port PICV				
⑨ 4-pipe with 6-port ball valve as changeover and PICV				

IAQ/CO2		Limits:	
	DC	U1 (*)	U1 (*)
	On/Off	Q3	

	en	de	es	fr	it	tr
①	2-pipe fan coil	2-Rohr Ventilator-konvektor	Fancoil a dos tubos	Ventiloconvecteur 2 tubes	Fan coil 2 tubi	2 borulu fan coil
②	2-pipe with electric heater	2-Rohranwendung & Elektroheizung	2 tubos & batería eléctrica	Application 2 tubes & batterie électrique	Fan coil 2 tubi con batteria elettrica	2 borulu & elk. Isıtıcı
③	2-pipe with radiator	2-Rohranwendung & Radiator	2 tubos & radiador	Application 2 tubes & radiateur	Fan coil 2 tubi e radiatore	2 borulu & radyatör
④	4-pipe fan coil	4-Rohr Ventilator-konvektor	Fancoil a 4 tubos	Ventiloconvecteur 4 tubes	Fan coil 4 tubi	4 borulu fan coil
⑤	2-pipe/2-stage	2-Rohr/2-stufig	2 tubos/2 etapas	2 tubes/2 étages	2-tubi / 2-stadi	2-borulu/2-kademe
⑥	4-pipe with electric heater	4-Rohranwendung & Elektroheizung	4 tubos & batería eléctrica	Application 4 tubes & batterie électrique	Fan coil 4 tubi con batteria elettrica	4 borulu fan coil & elk. Isıtıcı
⑦	4-pipe/2-stage	4-Rohr/2-stufig	4 tubos/2 etapas	4 tubes/2 étages	4-tubi / 2-stadi	4-borulu/2-kademe
⑧	4-pipe with 6-port ball valve	4-Rohr mit 6-Weg-Kugelventil	4 tubos con válvula de bola de 6 vías	4 tubes avec vanne à boisseau sphérique 6 voies	4-tubi con valvola a 6 vie	4-borulu, 6-yollu küresel vana
⑨	4-pipe with 6-port ball valve as changeover and PICV	4-Rohr mit 6-Weg-Kugelventil für Umschaltung und PICV	4 tubos con válvula de bola de 6 vías como cambio y PICV	4 tubes avec vanne à boisseau sphérique 6 voies comme changeover et PICV	4-tubi con valvola a 6 vie per commutazione stagionale e valvola PICV	4-borulu, PICV ve yaz kış geçişi için 6-yollu küresel vana
⑩	4-pipe with 6-port PICV	4-Rohr mit 6-Weg-PICV	4 tuberías con PICV de 6 puertos	4 tubes avec (vanne) PICV 6 voies	4-tubi con valvola a 6 vie PICV	4-Borulu 6-Yollu PICV vana