



SIVACON, door half, left, with cutout for filter fan, with ventilation openings, H: 2200 mm, W: 400 mm, RAL 7035, protection class 1

| Model                               |  |                             |       |
|-------------------------------------|--|-----------------------------|-------|
| product brand name                  |  | SIVACON                     |       |
| product designation                 |  | Door half                   |       |
| design of the product               |  | With cut-out for filter fan |       |
| design of the surface               |  | Powder-coated               |       |
| design of the product EMC version   |  | No                          |       |
| Protection class                    |  |                             |       |
| protection class IP                 |  | IPXX                        |       |
| operating resource protection class |  | safety class 1              |       |
| Appearance                          |  |                             |       |
| RAL color number                    |  | 7035                        |       |
| color                               |  | light grey                  |       |
| Product details                     |  |                             |       |
| product component                   |  |                             |       |
| • ventilation                       |  | Yes                         |       |
| • viewing door                      |  | No                          |       |
| • door for disconnecter lock        |  | No                          |       |
| Mechanical Design                   |  |                             |       |
| height                              |  | 2 200 mm                    |       |
| width                               |  | 400 mm                      |       |
| opening direction of the door       |  | left                        |       |
| material                            |  | steel                       |       |
| Approvals Certificates              |  |                             |       |
| General Product Approval            |  | Test Certificates           | other |



[Special Test Certificate](#)

[Confirmation](#)

[Miscellaneous](#)

|       |             |
|-------|-------------|
| other | Environment |
|-------|-------------|

[Miscellaneous](#)

Siemens  
EcoTech



[Environmental Confirmations](#)

| Further information                                                                                                                                                     |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Information on the packaging<br><a href="https://support.industry.siemens.com/cs/ww/en/view/109813875">https://support.industry.siemens.com/cs/ww/en/view/109813875</a> |

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1240-2UT25-3BA2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1240-2UT25-3BA2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MF1240-2UT25-3BA2](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1240-2UT25-3BA2)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

4/13/2025 

