



## MECCA PRO 1/2" SOCKET & TOOL SET 68 PIECES

- 12 point bi-hexagon sockets for easier alignment to the fastening
- A range of combination spanners, pliers and screwdrivers
- Chrome vanadium satin finish sockets and spanners
- Hard wearing case
- Tools clearly laid out to easily identify which tool belongs where
- Designed and manufactured to DIN and ISO standards

Tool Set 1/2" Drive Metric 68 Pieces

### General information

**Country of origin:** Taiwan  
**Barcode:** 5020385010895  
**Tarriff code Europe:** 8204200000  
**ECCN US:** EAR99  
**ETIM:** EC000149  
**UNSPSC:** 27111703

### Dimensions

**Net weight (g):** 6648  
**Width (mm):** 466  
**Depth (mm):** 258  
**Height (mm):** 103

### Attributes

**Product type:** Socket Sets  
**Material:** CrV  
**Certificates:** N/A  
**Number of pieces:** 68  
**Drive:** 1/2"  
**Socket type:** Regular, 12-point  
**Unit of measurement:** Metric

### Features



Technical changes and errors may occur. 01-08-2024 19:54



**DESIGNED IN SWEDEN**

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3  
 441 39 Alingsås, Sweden

# ADDITIONAL IMAGES



WWW.TENGOOLS.COM



# LIST OF CONTENTS



## **T1268** MECCA PRO 1/2" Socket & Tool Set 68 Pieces

<b>1200FRP</b>	1/2" Ratchet FRP 45 Teeth
<b>600508</b>	Combination Spanner Metric 8 mm
<b>600510</b>	Combination Spanner Metric 10 mm
<b>600511</b>	Combination Spanner Metric 11 mm
<b>600512</b>	Combination Spanner Metric 12 mm
<b>600513</b>	Combination Spanner Metric 13 mm
<b>600514</b>	Combination Spanner Metric 14 mm
<b>600515</b>	Combination Spanner Metric 15 mm
<b>600516</b>	Combination Spanner Metric 16 mm
<b>600517</b>	Combination Spanner Metric 17 mm
<b>600519</b>	Combination Spanner Metric 19 mm
<b>FL2507A03</b>	1/4" Flat Bits 25 mm 7 mm
<b>FL2508A03</b>	1/4" Flat Bits 25 mm 0.8 × 4.0 mm
<b>FL2508B03</b>	1/4" Flat Bits 25 mm 0.8 × 5.5 mm
<b>HEX2500303</b>	1/4" Hex Bits 25 mm 3 mm
<b>HEX2500403</b>	1/4" Hex Bits 25 mm 4 mm
<b>HEX2500503</b>	1/4" Hex Bits 25 mm 5 mm
<b>HEX2500603</b>	1/4" Hex Bits 25 mm 6 mm
<b>HEX2500803</b>	1/4" Hex Bits 25 mm 8 mm
<b>HEX2501003</b>	1/4" Hex Bits 25 mm 10 mm
<b>M120020-C</b>	1/2" Extension Bar 63.5 mm
<b>M120023-C</b>	1/2" Extension Bar 150 mm
<b>M120030-C</b>	1/2" Universal Joint
<b>M120510-C</b>	1/2" Socket 12 pt Metric 10 mm
<b>M120511-C</b>	1/2" Socket 12 pt Metric 11 mm
<b>M120512-C</b>	1/2" Socket 12 pt Metric 12 mm
<b>M120513-C</b>	1/2" Socket 12 pt Metric 13 mm
<b>M120514-C</b>	1/2" Socket 12 pt Metric 14 mm
<b>M120515-C</b>	1/2" Socket 12 pt Metric 15 mm
<b>M120516-C</b>	1/2" Socket 12 pt Metric 16 mm
<b>M120517-C</b>	1/2" Socket 12 pt Metric 17 mm
<b>M120518-C</b>	1/2" Socket 12 pt Metric 18 mm
<b>M120519-C</b>	1/2" Socket 12 pt Metric 19 mm
<b>M120521-C</b>	1/2" Socket 12 pt Metric 21 mm
<b>M120522-C</b>	1/2" Socket 12 pt Metric 22 mm
<b>M120524-C</b>	1/2" Socket 12 pt Metric 24 mm
<b>M120527-C</b>	1/2" Socket 12 pt Metric 27 mm
<b>M120530-C</b>	1/2" Socket 12 pt Metric 30 mm
<b>M120532-C</b>	1/2" Socket 12 pt Metric 32 mm
<b>M380036-C</b>	Step Up Adaptor 3/8"F - 1/2"M
<b>MB441-6</b>	Side Cutting Plier 160 mm

<b>MB452-7</b>	Heavy Duty Combination Plier 185 mm
<b>MB461-8</b>	Long Nose Plier 200 mm
<b>MB481-10</b>	Water Pump Plier 240 mm
<b>MD920N</b>	Flat Screwdriver 0.5 × 3.0 × 75 mm S
<b>MD922N</b>	Flat Screwdriver 1.0 × 5.5 × 75 mm S
<b>MD932N</b>	Flat Screwdriver 1.2 × 6.5 × 100 mm L Hex Shaft
<b>MD940N</b>	PH Screwdriver PH0 × 75 mm S
<b>MD947N1</b>	PH Screwdriver PH1 × 75 mm M
<b>MD952N</b>	PH Screwdriver PH2 × 100 mm L Hex Shaft
<b>PH2500003</b>	1/4" PH Bits 25 mm PH0
<b>PH2500103</b>	1/4" PH Bits 25 mm PH1
<b>PH2500203</b>	1/4" PH Bits 25 mm PH2
<b>PH2500303</b>	1/4" PH Bits 25 mm PH3
<b>PZ2500103</b>	1/4" PZ Bits 25 mm PZ1
<b>PZ2500203</b>	1/4" PZ Bits 25 mm PZ2
<b>PZ2500303</b>	1/4" PZ Bits 25 mm PZ3
<b>TX2500803</b>	1/4" TX Bits 25 mm TX8
<b>TX2501003</b>	1/4" TX Bits 25 mm TX10
<b>TX2501503</b>	1/4" TX Bits 25 mm TX15
<b>TX2502003</b>	1/4" TX Bits 25 mm TX20
<b>TX2502503</b>	1/4" TX Bits 25 mm TX25
<b>TX2502703</b>	1/4" TX Bits 25 mm TX27
<b>TX2503003</b>	1/4" TX Bits 25 mm TX30
<b>TX2504003</b>	1/4" TX Bits 25 mm TX40
<b>TX2504503</b>	1/4" TX Bits 25 mm TX45
<b>TX2505003</b>	1/4" TX Bits 25 mm TX50