

Floor standing encl. polyester vers.PLAT open top w/ canopy 1000x1250x320 IP44

Local distributor code:

403420779 NSYPLAT10123G

! Discontinued on: 9 Feb 2023

(!) Discontinued

EAN Code: 3606480775178

Main

Range	PanelSeT	
product name	PanelSeT PLA	
Enclosure type	Multi-purpose	
Product or component type	Suitable enclosure	
Version	PLAT	
Nominal height	1000 mm	
Nominal width	1250 mm	
Nominal depth	320 mm	
Enclosure mounting	Floor-standing	
Device composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 canopy	

Complementary

Body type	Open top and sealed bottom part assembled with side parts	
Door type	Plain front	
Number of doors	2 door(s)	
Door opening side	Right and left (120 °)	
Lock type	4 points lock, handle with 5 mm double bar insert	
Accessibility for operation	Top Rear Front	
Removable parts	Door by hinges Rear panel by fixing element Canopy by fixing element	
Material	Polyester reinforced with fibreglass	
Colour	Grey (RAL 7035)	
Standards	IEC 62208	
Product certifications	Veritas	
Electrical insulation class	Class II	

Environment

IP degree of protection	IP44 conforming to IEC 60529 (with ventilated canopy)	
IK degree of protection	IK10 conforming to IEC 62262 (plain door)	
Fire resistance	960 °C conforming to IEC 62208	
Ambient air temperature for storage	-3590 °C	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	38.000 cm
Package 1 Width	105.000 cm
Package 1 Length	129.000 cm
Package 1 Weight	51.000 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	2
Package 2 Height	115.000 cm
Package 2 Width	100.000 cm
Package 2 Length	130.000 cm
Package 2 Weight	115.000 kg

Logistical informations

Country of origin ES

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint		
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	397	
Environmental Disclosure	Product Environmental Profile	

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	1341ad4e-77b9-40e3-bab0-32043fbc5959

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No