



Dimmer for adjustable LED lamp and electronic transformers max.: 100 W

Model	
product brand name	DELTA
product designation	Dimmer
design of the product	Insert
type of load	other
type of composition	Basic element with complete enclosure
design of the actuating element	button
design of dimmer series dimmer	No
General technical data	
operating apparent power rated value	
• minimum	4 VA
• maximum	100 VA
dimming power minimum	4 VA
mounting type	Other
surface processing	other
material	other
Supply voltage	
operating voltage rated value	230 V
Protection class	
protection class IP	IP20
Main circuit	
operating frequency rated value	
• minimum	50 Hz
• maximum	50 Hz
Suitability	
suitability for interaction	
• motion detector	Yes
• radio key	Yes
• IR pushbutton	Yes
• presence detector	Yes
• pushbutton	Yes
• time switch	No
Appearance	
appearance	not applicable
color	white
Product details	
product component	
• light value memory	Yes
• extension input	No
product feature	

- halogen-free
- transparent

Yes
No

Mechanical Design

height	69 mm
width	95 mm
depth	12 mm
fastening method	flush mounting
material of the enclosure	plastic

Approvals Certificates

General Product Approval	Declaration of Con- formity	other
--------------------------	--------------------------------	-------

[Confirmation](#)



EG-Konf.

[Miscellaneous](#)

[Confirmation](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TC8211-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TC8211-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TC8211-0

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/23/2021

