



ITEM. 05545

SIP STARTMASTER PWT5500 STARTER CHARGER

HIGH-QUALITY BENCH DRILLING FOR HOME USERS & ENTHUSIASTS



COMES WITH
A 2-YEAR
STANDARD
WARRANTY*

FIND OUT MORE AT
SIP-GROUP.COM/WARRANTY



PRODUCT DESCRIPTION

The **SIP STARTMASTER PWT5500 Starter Charger** is an intelligent charger built with safe and automatic boost starting, along with 4 versatile charging levels and timer, and offers full compatibility with all Lead Acid, SLA, AGM, GEL, WET and VRLA batteries.

KEY FEATURES

- ✓ 12v/24v charging voltage and 300A max. boost rate
- ✓ Intelligent charging with battery type selection
- ✓ 4 versatile charging levels and charging timer
- ✓ Automatic battery maintainer on all batteries
- ✓ Clear and easy-to-read control panel

For over 50 years, SIP Industrial Products Limited has been a flagship supplier of high-quality equipment and machinery to the ever-growing engineering, construction, automotive, and agricultural marketplaces.



ITEM. 05545

SIP STARTMASTER PWT5500 STARTER CHARGER

ADDED FEATURES

- ✓ 12v/24v charging voltage and 300A max. boost rate
- ✓ 450Ah max. battery capacity and 30A charging current
- ✓ 4 different charge rate settings for added versatility
- ✓ Easy battery type selection for Lead Acid, SLA, AGM, GEL, WET, and VRLA
- ✓ Integrated charging timer and automatic battery maintainer on all types
- ✓ Safe Start function helps protect vehicle electronics
- ✓ Auto Boost Start offers one-man operation
- ✓ Wheel-mounted steel casing for increased mobility
- ✓ Remote lead for easy one-man operation
- ✓ Heavy-duty leads and crocodile clips
- ✓ Manufactured in Italy

APPLICATIONS & USES

Perfect for professional-grade workshops and garages.

TECHNICAL INFORMATION

ITEM NO.	05545
Input Supply:	230v (16A)
Output Voltages:	12v / 24v
Battery Capacity:	450Ah
Average Current Output:	30A (12v) / 15A (24v)
Max. Current Output:	45A (12v) / 22.5A (24v)
Max. Boost Current:	Fully discharged 300A / Medium discharged 200A
Internal Fuse Rating:	120A
Charge Rate Settings:	4 settings / boost
Compatible Battery Types:	PB, SLA, AGM, GEL, WET, VRLA
Net Weight:	17.60kg
Gross Weight:	19.30kg
Product Dimensions:	720(H) x 440(W) x 320mm(D)
Packaged Dimensions:	360(H) x 400(W) x 700mm(D)