

SMX 316L stainless monobloc enclosure, H2000xW1200xD500mm, Scotch Brite® finish.

NSYSMX201250H

### Main

Range	PanelSeT	
product name	PanelSeT SMX	
enclosure type	Multi-purpose	
category	Compact enclosure	
nominal height	2000 mm	
nominal width	1200 mm	
nominal depth	500 mm	
product installation	Floor-standing	
Device composition	1 body 2 door 1 cable gland plate 1 locking system with handle: door	
	4 mounting plate bracket	

## Complementary

Body type	Single piece body folded and welded	
Door type	Plain	
Door opening side	Reversible (120 °)	
Number of doors	Front face: 2 door(s)	
Lock type	3 points lock, handle with 5 mm double-bar insert	
Type of gland plate	Plain	
Accessibility for operation	Front	
Mounting plate description	Without mounting plate	
Material	Handle: zamak Hinge: stainless steel Body and door: stainless steel 316L	
Removable parts	Door by hinges Mounting plate bracket by screws Cable gland plate by clips	
Surface finish	Enclosure: Scotch-Brite® brushed Handle: painted	
Product weight	180 kg	

### **Environment**

Standards	IEC 62208
	UL
	CUL

IP degree of protection	IP55 conforming to IEC 60529	
IK degree of protection	IK10 conforming to IEC 62262	
Product certifications	UL 508 CAN/CSA 22	
Environmental characteristic	Corrosive Specific hygiene	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	213.000 cm
Package 1 Width	125.000 cm
Package 1 Length	59.000 cm
Package 1 Weight	161.000 kg

# **Contractual warranty**

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	2871
Environmental Disclosure	Product Environmental Profile

### **Use Better**

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	52da316e-d4e1-4114-85c0-32a03b2934fd
REACh Regulation	REACh Declaration

### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Image of product in real life situation

