


Lunettes EVOSpec®

Fumé / ANT120-200-000



DESCRIPTION

Protection oculaire rétractable en polycarbonate à utiliser avec les casques JSP EVO®. La lunette EVOSpec® est disponible en incolore et en fumé, offrant une protection contre la lumière nocive et les impacts à faible énergie. Simple à installer sur un casque EVO®, l'EVOSpec® garantit qu'une protection des yeux est toujours disponible en cas de besoin.

OPTIONS

Incolore (ANT010-200-000)

Fumé (ANT120-200-000)

NORMES

EN 172 • EN 166 • ANSI Z87. 1



INFORMATIONS TECHNIQUES



RADIATION PROTECTION BREAKDOWN filtering effect
Scale Number
5



LIGHT TRANSMISSION BREAKDOWN Lens Shade number
2,5



Manufacturer's Trademark
JSP dagger



Low Energy Impact resists a 6 mm, 0.86g ball @ 45 m/s °
Maximum protection for glasses
F



Optical Class (1 – Class 1 – High quality for regular use. 2 – Class 2 – Medium quality for occasional use. 3 – Class 3 – Low quality for exceptional use)
1



Resistance to fogging (optional)



The letter T, immediately after the mechanical strength symbol, authorises use for high speed particles at extreme temperatures. (-5°C and +55°C) Optional
T

CARACTÉRISTIQUES



Rétractable

Garantit que des lunettes de sécurité sont disponibles en cas de besoin, qu'elles ne sont jamais perdues et qu'elles sont protégées contre les dommages lorsqu'elles sont rétractées dans la calotte du casque.



Montage facile

Rapide et simple à installer sur les casques EVO®.



Oculaires disponibles

Les lunettes EVOSpec® sont disponibles en version incolore et fumée, offrant une protection contre les rayons UV, l'éblouissement, en plus d'une protection contre les impacts à faible énergie.

GAMME

VIDÉOS



youtu.be/LdxMNctXLbg

TÉLÉCHARGEMENTS

[Pack d'images \(ZIP\)](#)

[doc-evospec-updated-nb2797.pdf \(PDF\)](#)



JSP Limited. Worsham Mill. Minster Lovell. Oxford OX29 0TA. England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jspsafety.com / Web: www.jspsafety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jspsafety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 2 of 2 / Issued 26 Mar 2025 / Copyright 2018 - 2025. JSP Limited. All Rights Reserved.

