

PREMIUM WATERTITE



OTTER HIGH-CUT RIGGER BOOT

Description: Brown Water-Resistant Nubuck Leather High-cut Pull-up Boot

Size: UK 3-13 | US 4-14 | EU 36-48

Industries: Construction, Mining, Manufacturing, Heavy, Light and General Industries, Utilities, Oil and Gas, Transportation, Logistics

Standard: SR (EN ISO 20345:2022)



SKU	Toecap	Steel Midsole	Color	Outsole	Category
OWT805KW	Yes	Yes	Brown	Dual Density PU/TPU	S3

The Otter Premium Watertite range of safety footwear is specifically engineered for those working in frequently wet conditions. Crafted from premium waterproof oily nubuck leather, these boots deliver outstanding water-repelling capabilities. Additionally, the range features Otter's signature OrthoPX insoles constructed from PORON® XRD™, offering unmatched comfort for extended wear.

Features:

- Water resistant nubuck leather upper pull-on lugs.
- Ergonomic OrthoPX insoles provide longer-lasting shock absorption and help keep feet feeling fresher all day long.
- Insoles integrate Otter's PORON® XRD™ heel cushion insert which absorbs up to 90% of the most intense force (impact)* for exceptional comfort. Made from a patented soft ultra-low modulus material, this insert is positioned at the heel, where impact is greatest as your foot strikes the ground, and minimizes bounce from heavy objects.
- Enhanced taibrella lining to reduce abrasion when in contact with the skin.
- Non-woven fibre insole board
- Extra wide-fitting steel toecap provides extra comfort for toes and forefoot.

*As measured according to ASTM-F1614-C

- Toecap bumper protects against scuffing.
- Dual-density PU/TPU outsole for superior shock absorption.
- Excellent slip resistant sole delivers durable traction; SR (EN ISO 20345:2022); Anti-static.
- Sole resistant to oils and acids/alkalis.

Industry Applications:

- Recommended for indoor/outdoor works. Suitable for heavy, light and general industries.

Storage And Care:

- Footwear should be stored in their original packaging. Keep in an area that is not subject to rapid changes in temperature or humidity levels.

Care Instructions:

- Store shoes in a cool, dry and well-ventilated area after use.
- Remove excess dust or dirt with a brush.
- Remove any marks using a damp cloth and soap if necessary. Polish any grain or pigmented leathers using a commercially available shoe care product.

SOLE FEATURES



Puncture Resistant



Anti-Static



Slip Resistant



Mineral Oils Resistant



Organic Oils & Fats Resistant

TOECAP FEATURES



Steel Safety Toecap

COMFORT FEATURES



Wide Profile Toecap



Lightweight

FOOTWEAR FEATURES



Water Resistant Leather



Toe Bumper

King's Safety Footwear
Asia Pacific Headquarters
Level 25, UOA Corporate Tower Lobby B,
Avenue 10, The Vertical
59200 Bangsar South City
Kuala Lumpur, Malaysia

+603-2777 3948
 hsp.asean@honeywell.com
 www.pip-hsp.com

LEARN MORE



OTTER_OWT805KW | v01/25
© 2025 PIP | HSP