



## Sockets

40D

Product no. 01030005  
GTIN 4018754000302  
Model 40 D 5



### Label.

1/4 " Sockets Spanner size 5mm L.23mm

### Properties.

- bi-hex with AS-Drive profile
- 1/4" internal square drive
- HPQ® high performance steel, chrome-plated
- DIN 3124 / ISO 2725-1 / DIN EN 3709 / ASME B 107.5M


## Technologies and features.



### High Performance Quality (HPQ®)

Our HPQ® tool is made of wear-resistant high-performance steel, yet is thin-walled and lightweight. It withstands high torques and is ideal for work in confined spaces such as turbines.

## Technical drawing.



## Technical attributes.

|                              |                                                         |
|------------------------------|---------------------------------------------------------|
| Drive profile                | bi-hex AS-Drive                                         |
| Internal square drive (inch) | 1/4 "                                                   |
| d1                           | 7,9 mm                                                  |
| d2                           | 10,7 mm                                                 |
| d3                           | 4 mm                                                    |
| DIN                          | DIN 3124 / ISO<br>2725-1, DIN EN 3709,<br>ASME B 107.5M |
| Length mm (L)                | 23 mm                                                   |
| Width across flats [mm]      | 5 mm                                                    |
| t1                           | 4,5 mm                                                  |
| t2                           | 15 mm                                                   |

## Logistics data.

|                       |                     |
|-----------------------|---------------------|
| Depth mm (IFS)        | 23                  |
| Width mm (IFS)        | 11                  |
| Height mm (IFS)       | 11                  |
| WEEE/ElektroG         | nicht ear-pflichtig |
| Length (packed, mm)   | 80                  |
| Width (packed, mm)    | 50                  |
| Height (packed, mm)   | 18                  |
| Volume (packed, dm3)  | 0.072 dm3           |
| Art. no.              | 01030005            |
| Weight (gross, kg)    | 0,093               |
| Weight PAP (kg)       | 0,000               |
| Weight PVC (kg)       | 0,002               |
| GTIN                  | 4018754000302       |
| Country of origin AWR | GERMANY             |
| Region of origin      | Nordrhein-Westfalen |
| Customs tariff no.    | 82042000            |
| Packing standard      | 10                  |
| Weight                | 9 g                 |

## Variants.

| Art. no. | Model no. (ERP) | Description                             | GTIN          |
|----------|-----------------|-----------------------------------------|---------------|
| 01030005 | 40 D 5          | 1/4 " Sockets Spanner size 5mm L.23mm   | 4018754000302 |
| 01030006 | 40 D 6          | 1/4 " Sockets Spanner size 6mm L.23mm   | 4018754000319 |
| 01030007 | 40 D 7          | 1/4 " Sockets Spanner size 7mm L.23mm   | 4018754000326 |
| 01030008 | 40 D 8          | 1/4 " Sockets Spanner size 8mm L.23mm   | 4018754000333 |
| 01030009 | 40 D 9          | 1/4 " Sockets Spanner size 9mm L.23mm   | 4018754000340 |
| 01030010 | 40 D 10         | 1/4 " Sockets Spanner size 10mm L.23mm  | 4018754000357 |
| 01030011 | 40 D 11         | 1/4 " Sockets Spanner size 11mm L.23mm  | 4018754000364 |
| 01030012 | 40 D 12         | 1/4 " Sockets Spanner size 12mm L.23mm  | 4018754000371 |
| 01030013 | 40 D 13         | 1/4 " Sockets Spanner size 13mm L.23mm  | 4018754000388 |
| 01030014 | 40 D 14         | 1/4 " Sockets Spanner size 14mm L.24mm  | 4018754000395 |
| 01030055 | 40 D 5,5        | 1/4 " Sockets Spanner size 5,5mm L.23mm | 4018754000401 |

GTIN.



**STAHLWILLE Eduard Wille GmbH & Co. KG**

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0 · Fax: +49 202 4791-200  
info@stahlwille.de · [www.stahlwille.com](http://www.stahlwille.com) · Copyright by STAHLWILLE Eduard Wille GmbH & Co. KG, Wuppertal  
Copyright by STAHLWILLE Eduard Wille GmbH & Co. KG, Wuppertal