

Bocube Alu

Enclosure with smooth lid, graphite grey, covers anodised, hinged



BA 241306-7024

Order no.: 00115224

* = Available on request.

Characteristics

Colour of enclosure group

Graphite grey, similar to RAL 7024

Protection class

IP 66, 68 - 1,2m (2 hours), 69

Enclosure Material

Enclosure: GD Al Si 12, seal PU foamed;

Hinges / covers: Al Mg Si 0.5 powder-coated / natural-coloured anodised

The materials correspond to requirements set R1 or R7 acc. to DIN EN 45545-2 of hazard level HL3.

Scope of delivery

enclosure incl. hinge and fixing material

Important!

To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a pressure compensation element.

» Additional information

Technical documentation / Downloads

Technical drawings

3D product data in STEP format: Registration necessary

Product drawing in PDF format: 00115224 BA-241306-70243D.pdf (1.4 MB)

Product drawing in DXF format: 00115224 BA-241306-7024.dxf (2.9 MB)


20.09.2019

Dimensions

Dimensions

259 x 128 x 60 mm

Product drawing



Product information

Bocube Alu GB.pdf (1.3 MB)

Drawing for mechanical processing: 00115224 BA-241306-7024-G.dxf
(2.1 MB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable glands, ...)

Assembly Instructions

Bocube-Alu BA Gehaeusemontage Enclosure Assembly 00911501.pdf
(183.5 KB)

Works Test Certificates

690 WPZ-Bocube-Alu DE.pdf (178.0 KB)

690 WPZ-Bocube-Alu EN.pdf (172.5 KB)

Matching accessories



Wall brackets

00500204 BA WL 13 - 7024 For BA ..13..



Quick-release fastener

00430209 BA 13 SV-C-0 For BA ..13.. anodized



Pressure compensation membrane DAE

52011000 DAE-D11 Self-adhesive membrane \varnothing 11 mm



Mounting panels, laminated paper, 2 mm

00605200 BA MH 2413 For BA 2413..



DIN rails DIN EN 60715 TH 15, galvanised steel

22151902 TS 15 For BA 2413..



DIN rails DIN EN 60715 G 32, galvanised steel

22321902 TS 32 For BA 2413..



DIN rails DIN EN 60715 TH 35, galvanised steel

22351902 TS 35 For BA 2413..



Screws (SHR) and distance bolts (DIBLZ) for mounting bosses in plastic enclosures

59005049 SHR Z M4x8

KD = 8