




Selection of car geometry tools - foam module 5/5

CPP-FREMM-2

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:07





DESCRIPTION



Selection of car geometry tools - foam module 5/5

- x1 3/8" wrench, length 600 mm
- x1 extension + 1/2" lever
- x1 10.2 mm anti-vibration chipper
- x1 set of ten 3/8" open-ended wrenches
- x1 socket for steering bearing
- x1 slotted socket 48X52
- x1 ball-tool retention
- x1 riveting die
- x1 open-ended wrench, 21 1/2"
- x1 bearing axial wrench, 28-35 mm

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:07



- x1 camber setting tool
- x2 bearing extractor on pivots
- x1 Stillson wrench, 10"
- x1 Stillson wrench, 18"
- x1 set of 4 force levers (210 mm, 310 mm, 410 mm and 610 mm)
- x1 ball joint puller for steering axial bearing, 35 to 45 mm
- x1 steering wheel setting level
- x2 car and van bearing extractor

SPECIFIC DATA

Designation	FOAM MODULE BRAKING COMPOSITION 32 TOOLS
Sales reference	CPP-FREMM-2
Weight (g)	11555
Number of tools	32
Guarantee	O SAM TOOL guarantee.

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

Toolset



x 1

Brake fluid tester with boiling point
FET-7B



x 1

Caliper for brake disc
3510B

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å.~

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:07



	x 1	Gauge for brake drum 76-MTVL-2
	x 1	Set of 4 clamps for flexible pipes FT-4
	x 2	Set of hexagonal flare nut ring wrenches in mm 104-H-... Ref : 104-H-11X13 - 104-H-12X14
	x 2	Set of 2 for braking hydraulic union FHTN-... Ref : FHTN-10X11 - FHTN-12X14
	x 1	Tool for spring 3100
	x 1	Side spring retainer with hook 3103
	x 1	Tool for side spring with cup 3102
	x 1	Hook spring removal 3100-2
	x 1	Handbrake cable clamps 208-15
	x 1	Down brake pad cleaning file 2760
	x 1	Wire brush 2880
	x 1	Tool for striking cap hub 3108-2
	x 1	Set of impact screwdrivers 270A-J6
	x 1	1/2" impact screwdriver 270-A

	x 1	1/2" standard bit holder sockets SD-1
	x 2	Box of 5 bits 5/16" impact slotted E-414-F... Ref : 9 11
	x 2	Box of 5 bits 5/16" impact Phillips® E-414-PH... Ref : 2 3
	x 2	Torx® impact sockets 1/2" NS-TX-... Ref : NS-TX-12 - NS-TX-16
	x 2	1/2" screwdriver socket - hexagonal SC-...1/2_6_pans Ref : SC-5-7 - SC-5-8
	x 3	Impact screwdriver socket 1/2" footprint XZN® 19152-... Ref : 19152-514 - 19152-516 - 19152-518
	x 3	5 sides socket 1/2" 10 mm 3122-... Ref : 3122-10 - 3122-14 - 3122-19
	x 1	Set of 3 locking electric screwdriver adapters EPM-J3
	x 1	Flange brake calliper pneumatic pushing tool 3112-90
	x 1	Brake fluid pencil tester FET-5J
	x 1	8 brake lining thickness gauge FD-J8