



Cable tie, Thorsman installation material, 550x8.8mm, clear

IMT46426

Main

| product range | Thorsman | |
|----------------------|--------------------------------|--|
| Range of product | Thorsman installation material | |
| product type | Cable tie | |
| colour | Clear | |
| quantity per package | Set of 100 | |

Complementary

| Minimum tightening diameter | 8.5 mm | |
|-----------------------------|----------------------------------|--|
| Maximum tightening diameter | 163.5 mm | |
| Condition of use | Indoor | |
| resistance to tearing | Resistance to tearing: 800 N | |
| Material | PA (polyamide) 6.6 UV-stabilised | |
| Length | 550 mm | |
| Width | 8.8 mm | |
| Thickness | 1.8 mm | |
| Net weight | 0.850 kg | |
| Market segment | Small commercial | |

Environment

| Environmental characteristic | Fire resistance needle flame 30 s conforming to IEC 60695-11-5 | |
|---------------------------------------|--|--|
| Flame retardance | Self-extinguishing conforming to UL 94 V2 | |
| Ambient air temperature for operation | -4085 °C | |

Packing Units

| Unit Type of Package 1 | PCE |
|------------------------------|--------|
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5.4 cm |
| Package 1 Width | 20 cm |
| Package 1 Length | 70 cm |
| Package 1 Weight | 904 g |
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 10 |

| Package 2 Height | 13 cm |
|------------------------------|-----------|
| Package 2 Width | 28.5 cm |
| Package 2 Length | 76.5 cm |
| Package 2 Weight | 10.04 kg |
| Unit Type of Package 3 | P12 |
| Number of Units in Package 3 | 280 |
| Package 3 Height | 105 cm |
| Package 3 Width | 80 cm |
| Package 3 Length | 120 cm |
| Package 3 Weight | 295.82 kg |

Contractual warranty

Warranty 18 mois



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

| ∅ Environmental footprint | |
|---|-------------------------------|
| Carbon footprint (kg.eq.CO2 per CR, Total Life cycle) | 1 |
| Environmental Disclosure | Product Environmental Profile |

Use Better

| Packaging made with recycled cardboard | Yes |
|--|--|
| Packaging without single use plastic | No |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| REACh Regulation | REACh Declaration |
| Halogen content performance | Halogen free product |
| PVC free | Yes |

Use Again

| ○ Repack and remanufacture | |
|----------------------------|--|
| Circularity Profile | No need of specific recycling operations |
| Take-back | No |