

3554 // ULTIMATE GRIP

Assembly gloves
PPE risk category II



Touchscreen capable
Ultimate grip
Very high abrasion resistance

18
GAUGE

NI



GRIP
CONTROL

3554 // ULTIMATE GRIP



Material:	Polyester, black
Coating:	Nitrile, red Nitrile foam, black
Size(s):	7-11
Packaging unit:	72 pair(s)
Certification:	EN 388, EN 407

NITRAS ULTIMATE GRIP, assembly gloves, black, double layer coating, lower coating: nitrile, red, partly coated, upper coating: special coating, black, (colour code: 1060), partly coated on palm and fingertips, knitted wrist, highest dexterity, water-repellent, protection against contact heat (100° C, 15 seconds), touchscreen capable, very slip resistant, ultimate grip thanks to Grip Control, very high abrasion resistance, very good dry and oil grip, PPE risk category II



EN ISO 21420



Size	7	8	9	10	11
Colour coding system					

Industries

-  Craft
-  Building / Construction
-  Automotive manufacturing
-  Commissioning / shipping
-  Landscape gardening

Advantages

- + Touchscreen capable
- + Ultimate grip
- + Very high abrasion resistance



Performance values

EN 388:2016 + A1:2018	Test parameter	Performance levels	Test result
 4121A	Abrasion resistance	1-4	4
	Blade cut resistance (Coupe-Test)	1-5	1
	Tear resistance	1-4	2
	Puncture resistance	1-4	1
	Blade cut resistance (TDM)	A-F	A
EN 407:2020	Test parameter	Performance levels	Test result
 X1XXXX	Resistance to flammability	1-4	X
	Contact heat resistance	1-4	1
	Convective heat resistance	1-4	X
	Radiant heat resistance	1-4	X
	Resistance to small splashes of molten metal	1-4	X
	Resistance to large quantities of molten metal	1-4	X
EN ISO 21420:2020 + A1:2024	Test parameter	Performance levels	Test result
	Dexterity	1-5	5

Additional information

	Material	Colour
Palm	Nitrile foam on nitrile and polyester, partially recycled	black
Index finger and thumb	Nitrile foam on nitrile and polyester, partially recycled	black / red
Back of the hand	Polyester	black
Fingertips	Nitrile foam on nitrile and polyester, partially recycled	black / red
Cuff / knitted wrist	Polyester	red

Logistics data

Size	GTIN (SPU)	GTIN (PU)	Length (m)	Width (m)	Height (m)	Weight (kg)	Quantity PU / pallet
7	4059904229655	4059904229648	0,46 m	0,37 m	0,24 m	8,5 kg	72
8	4059904229679	4059904229662	0,46 m	0,37 m	0,24 m	8,6 kg	72
9	4059904229693	4059904229686	0,46 m	0,37 m	0,24 m	8,7 kg	72
10	4059904229716	4059904229709	0,46 m	0,37 m	0,24 m	8,8 kg	72
11	4059904229730	4059904229723	0,46 m	0,37 m	0,24 m	8,9 kg	72

Customs tariff number: 61161020910

Country of origin: China