

ATPS 2324 desktop power supply
MODEL : 9832H FOR INDOOR USE ONLY
INPUT : AC100-240V 50 / 60Hz 800mA
OUTPUT : DC12V-24V MAX. 30VA
 CONFORMS TO ANSI/UL STD. 850
 CERTIFIED TO CAN/CSA STD. C22.2 NO. 950
CE
 PLEASE BE SURE TO SELECT THE CORRECT POLARITY AND VOLTAGE BEFORE CONNECTING YOUR EQUIPMENT. DO NOT ALTER THE VOLTAGE OR CHANGE POLARITY DURING POWER OPERATION
 part.no. 8694001/01
AN-MANN Germany

LED grün/green
 Spannungswahlschalter/
 voltage switch-over plug

Klinkenstecker/
 jackplug
 ø2,5x12mm

Hohlstecker/
 hollowplug
 ø2,1xø5x12mm

Hohlstecker/
 hollowplug
 ø2,35xø0,75x10mm

Hohlstecker/
 hollowplug
 ø1,75xø4,75x10mm

Hohlstecker/
 hollowplug
 ø2,5xø5,5x12mm

Hohlstecker/
 hollowplug
 ø1,35xø3,5x10mm

Hohlstecker/
 hollowplug
 ø1,7xø4x10mm

Klinkenstecker/
 jackplug
 ø3,5x15mm

1 **423-9252** 
ATP2324
Made in China


gelber Aufkleber
auf Faltschachtel
yellow label on
the folding box

Zusatzinfos/ more informations	: Sollten zu dem aufgeführten Produkt nähere technische Informationen gewünscht werden, können diese unter der Angabe der jeweiligen Artikel Nr. als Adobe PDF-File kostenlos angefordert werden/ If you need more technical informations about this product, you can ask for an gratis data sheet as Adobe PDF-file by indicating the part No.
-----------------------------------	--

Verwendungsbereich/Application range für Anfrage/for inquiry xxx/xx				Zul. Abweichung/ Allowable deviation		Oberfläche/ Surface		Maßstab/Scale 1:1		Gewicht/Weight	
								Werkstoff/Work material, Modell-Nr. XXX			
Entwicklung/ Development	Geprüft/Checked by	Datum/date	Name								
Vertrieb/ Distribution	✓	07.12.05	KR	2001	Datum/Date	Name					
				Bearbeitet/ Drawn by	10.12.	AS					
				Geprüft/ Checked by	07.12.05	AS					
V1	rating plate; WEEE sign added	07.12.05	AS					Zeichnungsnummer/Drawing number		Blatt/ Sheet 1	
V1	datasheet design changed	06.04.05	OB					Artikelnummer/Part number			
V1	rating plate updated	07.06.04	SM								
Version	Änderung/Change	Datum/Date	SM	Ursprung/Origin	Proj. XX/XX/XX	Ersatz für/Replaced by		Ersatz durch/Replacement through:			