



OUR OFFER

Allen-Bradley – Micro800

Micro800 - Controller

Programmable Controller Family
Designed for low-cost , standalone machines

Micro810

Stock-No.	MPN	In/Out	Output	Communication
750-8602	2080-LC10-12QWB	8/4	Relay	USB (with Adapter)
750-8605	2080-LC10-12AWA	8/4	Relay	USB (with Adapter)
750-8609	2080-LC10-12QBB	4/4	24Vdc Source	USB (with Adapter)



Micro820

Stock-No.	MPN	In/Out	Output	Communication
893-7767	2080-LC20-20QBB	12/8	24Vdc Source	Ethernet, RS232, RS485
893-7761	2080-LC20-20QWB	12/8	Relay	Ethernet, RS232, RS485
893-7770	2080-LC20-20AWB	12/8	Relay	Ethernet, RS232, RS485



Micro830

Stock-No.	MPN	In/Out	Output	Communication
750-8618	2080-LC30-10QWB	6/4	Relay	USB, RS232, RS485
750-8611	2080-LC30-16QWB	10/6	Relay	USB, RS232, RS485
750-8624	2080-LC30-24QWB	14/10	Relay	USB, RS232, RS485
750-8621	2080-LC30-48QWB	28/20	Relay	USB, RS232, RS485



Micro830 - Starter Kit

Stock-No.	MPN	In/Out	Output	Communication
750-8674	2080-START830-24	14/10	Transistor	USB, RS232, RS485
750-8677	2080-START830-48	28/20	Transistor	USB, RS232, RS485

Micro850

Stock-No.	MPN	In/Out	Output	Communication
786-7197	2080-LC50-24AWB	14/10	Relay	USB, Ethernet, RS232, RS485
786-7190	2080-LC50-24QBB	14/10	24Vdc Source	USB, Ethernet, RS232, RS485
786-7194	2080-LC50-24QVB	14/10	24Vdc Sink	USB, Ethernet, RS232, RS485
786-7204	2080-LC50-24QWB	14/10	Relay	USB, Ethernet, RS232, RS485
786-7207	2080-LC50-48AWB	28/20	Relay	USB, Ethernet, RS232, RS485
786-7201	2080-LC50-48QBB	28/20	24Vdc Source	USB, Ethernet, RS232, RS485
786-7210	2080-LC50-48QVB	28/20	24Vdc Sink	USB, Ethernet, RS232, RS485
786-7213	2080-LC50-48QWB	28/20	Relay	USB, Ethernet, RS232, RS485



For more technical information please visit:

www.rs-online.com