

FEATURES

- Six-piece high-quality screwdriver set
- Ergonomic handles
- Convenient tool wrap

RS PRO Engineers Slotted Parallel; Slotted Flared; Pozidriv Screwdriver Set 6 Piece

RS Stock No.: 459-3944



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted RS PRO brand, this high-quality and versatile screwdriver set is ideal for engineering applications. With a selection of flared and parallel flat-headed and pozidriv screwdrivers included, the set is able to tackle screws and fasteners of various common sizes. With chrome vanadium steel blades, these screwdrivers are highly durable and resistant to corrosion.

General Specifications

Screwdriver Type	Engineers
Number of Pieces	6
Tip Type	Slotted Parallel; Slotted Flared; Pozidriv
Set Contents	<p>4pc- Flare tip slotted screwdriver with Red/Black colour double injection handle; Sizes 5.0x75mm, 5.0x100mm, 6x 150mm, Chubby: 6x 40mm</p> <p>4pc- Parallel tip slotted screwdriver Red/Black colour double injection handle Sizes 3.0x50mm, 3z100mm, 3x 150mm, 5x 200mm</p> <p>4pc- Pozidriv screwdriver with Red /Black colour double injection handle; Sizes No.0 x 75mm, No. 1 x75mm, No.2 x 100mm, Chubby No .2 x 40mm</p> <p>1pc- VDE insulated pozidriv screwdriver with Red/Black colour double injection handle; Size No. 1 x80mm</p> <p>5pc- Phillips screwdriver with Red/Black colour double injection handle Sizes No. 0x 50mm, No. 1 x 75mm, No. 2 x 100mm, No. 3x 150mm, Chubby no.1 x 40mm (Remove the magnet from tip)</p>
Applications	Electricians, Maintenance engineers, DIY enthusiasts

Mechanical Specifications

Tip Size	Slotted Parallel: 3mm; 5mm; Slotted Flared: 5mm; 6mm; Pozidriv: PZ1; PZ2
Blade Material	Phillips and Pozidriv tips: Chrome Molybdenum Vanadium steel (S-2) Slotted Tips: Chrome Vanadium steel (#6155)
Handle Material	Polypropylene / TPR handle
Blade Finish	Satin chrome finish and Phosphate Black tip
Hardness	Phillips and Pozidriv tips: Heat treat to HRC 58-62 degrees Slotted tips: Heat treat to HRC 52-56 degrees

