

WT-BASE LS HF 6 BK - Cable binder base



3240709

<https://www.phoenixcontact.com/gb/products/3240709>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable binder base, for cable binders up to 6 mm wide, self-adhesive (rubber) and screwable, 4.8 mm fixing hole, 4-sided cable binder feed-through



Commercial data

Item number	3240709
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BE713Z
Product key	BE713Z
Catalog page	Page 622 (C-3-2019)
GTIN	4046356703963
Weight per piece (including packing)	1.693 g
Weight per piece (excluding packing)	1.697 g
Customs tariff number	39269097
Country of origin	HR

WT-BASE LS HF 6 BK - Cable binder base



3240709

<https://www.phoenixcontact.com/gb/products/3240709>

Technical data

Product properties

Product type	Cable tie
Type	Fixing
Tensile strength GRP	220 N

Dimensions

Width	27 mm
Height	6.5 mm
Length	27 mm
Hole diameter	4.8 mm
Diameter mounting hole	4.8 mm

Internal dimensions

Width_inside	6 mm
--------------	------

Material specifications

Color	black (RAL 9005)
Material	ABS
Flammability rating according to UL 94	HB
Components	free from silicone and halogen

Cable/line

Tensile strength	220 N
------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (assembly)	15 °C ... 40 °C

Mounting

Mounting type	Screw mounting
	adhesive

WT-BASE LS HF 6 BK - Cable binder base



3240709

<https://www.phoenixcontact.com/gb/products/3240709>

Classifications

ECLASS

ECLASS-13.0	23159090
-------------	----------

ETIM

ETIM 9.0	EC011571
----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

WT-BASE LS HF 6 BK - Cable binder base



3240709

<https://www.phoenixcontact.com/gb/products/3240709>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk