

Floor standing polyester enclosure, PanelSeT PLA, plain door, open bottom, 750x750x620mm, IP54, IK10

NSYPLAZ776G

### Main

Range	PanelSeT
product name	PanelSeT PLA
Enclosure type	Multi-purpose
Product or component type	Suitable enclosure
Version	PLAZ
Nominal height	750 mm
Nominal width	750 mm
Nominal depth	620 mm
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 2 side part 1 rear panel 1 door 1 plinth

## Complementary

Body type	Sealed top and open bottom part assembled with side parts	
Door type	Plain front	
Number of doors	1 door(s)	
Door opening side	Reversible (120 °)	
Lock type	2 points handle lock, 5 mm double-bar	
Accessibility for operation	Rear Bottom Front	
Removable parts	Door by hinges Rear panel by fixing element	
Material	Polyester reinforced with fibreglass	
Colour	Grey (RAL 7035)	
Standards	IEC 62208	
Product certifications	Veritas	
Electrical insulation class	Class II	

## **Environment**

IP degree of protection IP54 conforming to IEC 60529 (plinth type open bottom)

IK degree of protection	IK10 conforming to IEC 62262 (plain door)	
Fire resistance	960 °C conforming to IEC 62208	
Ambient air temperature for storage	-3590 °C	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	66.000 cm
Package 1 Width	78.000 cm
Package 1 Length	82.000 cm
Package 1 Weight	31.800 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	2
Package 2 Height	182.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	75.600 kg



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint		
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	247	
Environmental Disclosure	Product Environmental Profile	

### **Use Better**

Materials and Packaging	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	1341ad4e-77b9-40e3-bab0-32043fbc5959
REACh Regulation	REACh Declaration

### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No