



Socket and Bits Set T Handle 62 Pieces

## T-HANDLE BITS DRIVER SET TT1 62 PIECES

- Comprehensive selection of 25mm 1/4" drive hex bits included
- T-handle bits driver with quick chuck adaptor on the long end and a magnetic bits holder on the short end
- Organised in a tool tray module size 1 (TT1)

### General information

**Country of origin:** Taiwan  
**Barcode:** 5020385064089  
**Tarriff code Europe:** 8207909900  
**ECCN US:** EAR99  
**ETIM:** EC002120  
**UNSPSC:** 27112814

### Dimensions

**Net weight (g):** 807  
**Width (mm):** 142  
**Depth (mm):** 265  
**Height (mm):** 50

### Attributes

**Product type:** Bits & Driver Sets  
**Certificates:** N/A  
**Number of pieces:** 62  
**Drive:** 1/4", 1/4" Hex  
**Inlay material:** PS  
**Type of set:** TT1

### Features



Technical changes and errors may occur. 01-08-2024 19:49



**DESIGNED IN SWEDEN**

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3  
 441 39 Alingsås, Sweden

# ADDITIONAL IMAGES



WWW.TENGOOLS.COM



# LIST OF CONTENTS



## **TTTHQ62** T-Handle Bits Driver Set TT1 62 Pieces

<b>FL2506A03</b>	1/4" Flat Bits 25 mm 0.6 × 3.5 mm
<b>FL2510A03</b>	1/4" Flat Bits 25 mm 1.0 × 5.5 mm
<b>FL2516A03</b>	1/4" Flat Bits 25 mm 1.6 × 8.0 mm
<b>GR25002010</b>	1/4" PH G Bits 25 mm PH2G
<b>GR25002010</b>	1/4" PH G Bits 25 mm PH2G
<b>GR25002010</b>	1/4" PH G Bits 25 mm PH2G
<b>HEX2500203</b>	1/4" Hex Bits 25 mm 2 mm
<b>HEX2500303</b>	1/4" Hex Bits 25 mm 3 mm
<b>HEX2500403</b>	1/4" Hex Bits 25 mm 4 mm
<b>HEX2500503</b>	1/4" Hex Bits 25 mm 5 mm
<b>HEX2500603</b>	1/4" Hex Bits 25 mm 6 mm
<b>HEX2500803</b>	1/4" Hex Bits 25 mm 8 mm
<b>M140039</b>	Hex Socket Adaptor 1/4" Hex - 1/4" 30 mm
<b>M140505-C</b>	1/4" Socket 6 pt Metric 5 mm
<b>M1405055-C</b>	1/4" Socket 6 pt Metric 5.5 mm
<b>M140506-C</b>	1/4" Socket 6 pt Metric 6 mm
<b>M140507-C</b>	1/4" Socket 6 pt Metric 7 mm
<b>M140508-C</b>	1/4" Socket 6 pt Metric 8 mm
<b>M140509-C</b>	1/4" Socket 6 pt Metric 9 mm
<b>M140510-C</b>	1/4" Socket 6 pt Metric 10 mm
<b>M140511-C</b>	1/4" Socket 6 pt Metric 11 mm
<b>M140512-C</b>	1/4" Socket 6 pt Metric 12 mm
<b>M140513-C</b>	1/4" Socket 6 pt Metric 13 mm
<b>M140704-C</b>	1/4" TX-E Socket E4
<b>M140705-C</b>	1/4" TX-E Socket E5
<b>M140706-C</b>	1/4" TX-E Socket E6
<b>M140707-C</b>	1/4" TX-E Socket E7
<b>M140708-C</b>	1/4" TX-E Socket E8
<b>MDTHQ</b>	1/4" T Handle Quick Chuck Bits Driver
<b>PH2500103</b>	1/4" PH Bits 25 mm PH1
<b>PH2500203</b>	1/4" PH Bits 25 mm PH2
<b>PH2500303</b>	1/4" PH Bits 25 mm PH3
<b>PZ2500103</b>	1/4" PZ Bits 25 mm PZ1
<b>PZ2500203</b>	1/4" PZ Bits 25 mm PZ2
<b>PZ2500303</b>	1/4" PZ Bits 25 mm PZ3
<b>ROB2500103</b>	1/4" ROB Bits 25 mm ROB1
<b>ROB2500203</b>	1/4" ROB Bits 25 mm ROB2
<b>ROB2500303</b>	1/4" ROB Bits 25 mm ROB3
<b>TPX2501003</b>	1/4" TPX Bits 25 mm TPX10
<b>TPX2501503</b>	1/4" TPX Bits 25 mm TPX15
<b>TPX2502003</b>	1/4" TPX Bits 25 mm TPX20

<b>TPX2502003</b>	1/4" TPX Bits 25 mm TPX20
<b>TPX2502503</b>	1/4" TPX Bits 25 mm TPX25
<b>TPX2502503</b>	1/4" TPX Bits 25 mm TPX25
<b>TPX2502703</b>	1/4" TPX Bits 25 mm TPX27
<b>TPX2503003</b>	1/4" TPX Bits 25 mm TPX30
<b>TPX2504003</b>	1/4" TPX Bits 25 mm TPX40
<b>TX2500603</b>	1/4" TX Bits 25 mm TX6
<b>TX2500703</b>	1/4" TX Bits 25 mm TX7
<b>TX2500803</b>	1/4" TX Bits 25 mm TX8
<b>TX2500903</b>	1/4" TX Bits 25 mm TX9
<b>TX2501003</b>	1/4" TX Bits 25 mm TX10
<b>TX2501503</b>	1/4" TX Bits 25 mm TX15
<b>TX2502003</b>	1/4" TX Bits 25 mm TX20
<b>TX2502003</b>	1/4" TX Bits 25 mm TX20
<b>TX2502003</b>	1/4" TX Bits 25 mm TX20
<b>TX2502503</b>	1/4" TX Bits 25 mm TX25
<b>TX2502503</b>	1/4" TX Bits 25 mm TX25
<b>TX2502503</b>	1/4" TX Bits 25 mm TX25
<b>TX2502703</b>	1/4" TX Bits 25 mm TX27
<b>TX2503003</b>	1/4" TX Bits 25 mm TX30
<b>TX2504003</b>	1/4" TX Bits 25 mm TX40