

LONG LIFE CUTTING HOLES IN MULTI MATERIAL

EXPERT Multi Material PC Plus Hole Saw

EXPERT

- ① Exceptional durability is built in with Bosch Carbide Technology
- ② Ground and sharpened fine carbide teeth for strength, durability and precision
- ③ Special slot design for better view and plug ejection



* vs. Bosch 2608580419



BOSCH

EXPERT MULTI MATERIAL PC PLUS HOLE SAW



- Ideal for cutting neat holes up to 60 mm in depth, for example for tubing for electricians' wires and plumbers' fresh & waste water pipes; holes for sockets, light switches, junction boxes; holes for recessed lighting, fire alarms, presence detectors; or for ducting for cool-air or drying air
- Best for electricians and plumbers: long lasting and highly versatile
- Lasts up to 50x longer than Bosch 2608580419 Hole Saw in tough materials
- For use with the Bosch Power Change Plus keyless arbor: offering accuracy and robustness



PRODUCT PROPERTIES			ORDERING INFORMATION				
Diameter mm	Working length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number	
20	60	PC1b	1	1	535 654	2 608 900 419	
22	60	PC1b	1	1	535 661	2 608 900 420	
25	60	PC1b	1	1	535 678	2 608 900 421	
32	60	PC1b	1	1	535 685	2 608 900 422	
35	60	PC1b	1	1	535 692	2 608 900 423	
38	60	PC1b	1	1	535 708	2 608 900 424	
40	60	PC1b	1	1	535 715	2 608 900 425	
44	60	PC1b	1	1	535 722	2 608 900 426	
51	60	PC1b	1	1	535 739	2 608 900 427	
54	60	PC1b	1	1	535 746	2 608 900 428	
57	60	PC1b	1	1	693 248	2 608 901 878	
60	60	PC1b	1	1	535 753	2 608 900 429	
64	60	PC1b	1	1	535 760	2 608 900 430	
65	60	PC1b	1	1	535 777	2 608 900 431	
67	60	PC1b	1	1	535 784	2 608 900 432	
68	60	PC1b	1	1	535 791	2 608 900 433	
70	60	PC1b	1	1	535 807	2 608 900 434	
73	60	PC1b	1	1	535 814	2 608 900 435	
76	60	PC1b	1	1	535 821	2 608 900 436	
80	60	PC1b	1	1	535 838	2 608 900 437	
83	60	PC1b	1	1	535 845	2 608 900 438	
102	60	PC1b	1	1	535 852	2 608 900 439	
105	60	PC1b	1	1	535 869	2 608 900 440	
111	60	PC1b	1	1	535 876	2 608 900 441	
114	60	PC1b	1	1	535 883	2 608 900 442	
127	60	PC1b	1	1	535 890	2 608 900 443	
152	60	C1a	1	1	535 906	2 608 900 444	



BOSCH