

Product data sheet

Specifications



Repacked Cover frame, New Unica, 1 gang, 2 modules, white

NU400218W



This repacked option saves 0.122 over the standard condition

Main

Range	New Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Pro
Number of gangs	1 gang
Installation direction	Horizontal/vertical
Type of frame	Single
Number of modules	2 modules
fixing mode	Clip-in
Colour tint	White (RAL 9003)

Complementary

Material	Thermoplastic ABS-UV stabilised: cover frame Polycarbonate: intermediate plate
Surface finish	Glossy
Standards	IEC 60669-1 IEC 60884-1
Width	85 mm
Height	85 mm
Depth	10 mm
Product weight	0.018 kg
resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IK degree of protection	IK04
IP degree of protection	IP21D

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of Units in Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	9.000 cm
Package 1 Length	9.700 cm
Package 1 Weight	19.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	100
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.204 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.1 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

59bc1733-7007-4ba6-bfd5-f7904c7d9a13

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No