

Device connector, front mounting - PRC FT25-0-HSG - 1065795

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Circular connectors (device-side), Range of articles: PRC, Device connector, front mounting, housing material: PPE, color: black, nom. voltage: 690 V AC

Your advantages

- ✓ Universal accommodation of existing connector heads with screw connection technology
- ✓ Modular system for optimized storage
- ✓ Versatile interfaces, thanks to straight and angled connector housings
- ✓ Ideal for indoor and outdoor use, thanks to the use of weatherproof materials



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 728384
GTIN	4055626728384
Weight per Piece (excluding packing)	30.000 g
Custom tariff number	39269097
Country of origin	Poland
Note	Made to Order (non-returnable)

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 9.0	27440103
------------	----------

Device connector, front mounting - PRC FT25-0-HSG - 1065795

Classifications

ETIM

ETIM 6.0	EC002061
----------	----------

Accessories

Accessories

Circular connector (cable-side)

Contact insert - PRC 5-HEAD-FS6-1 - 1070197



Circular connectors (cable-side), Range of articles: PRC, Contact insert, type: Release with tool or by hand (see accessories), housing material: PPE, color: black, number of positions: 5, min. conductor cross section: 1.5 mm², max. conductor cross section: 6 mm², nom. voltage: 690 V AC, rated current: 35 A, Connection method: Screw connection, Type of contact: Socket

Contact insert - PRC 3-HEAD-FS6-1 - 1070198



Circular connectors (cable-side), Range of articles: PRC, Contact insert, type: Release with tool or by hand (see accessories), housing material: PPE, color: black, number of positions: 3, min. conductor cross section: 1.5 mm², max. conductor cross section: 6 mm², nom. voltage: 690 V AC, rated current: 35 A, Connection method: Screw connection, Type of contact: Socket

Contact insert - PRC 5-HEAD-MS6-2 - 1070199



Circular connectors (cable-side), Range of articles: PRC, Contact insert, housing material: PPE, color: black, number of positions: 5, min. conductor cross section: 1.5 mm², max. conductor cross section: 6 mm², nom. voltage: 690 V AC, rated current: 35 A, Connection method: Screw connection, Type of contact: Pin

Contact insert - PRC 3-HEAD-MS6-2 - 1070200



Circular connectors (cable-side), Range of articles: PRC, Contact insert, housing material: PPE, color: black, number of positions: 3, min. conductor cross section: 1.5 mm², max. conductor cross section: 6 mm², nom. voltage: 690 V AC, rated current: 35 A, Connection method: Screw connection, Type of contact: Pin