

TECHNICAL DATA

**Polycarbonate Bowl Combination Emergency Shower & Eyewash |
Polycarbonate Bowl Combination Emergency Shower &
Eyewash with Foot Pedal**
Model: PG 10020 AB | PG 10022 AB

PROGUARD[®]
Your Ultimate Partner In Safety[®]

Our combination unit of drench and eyewash is popular in workplace where fire and chemical spillages may occur. All control valves are instant action, stay open type of ball valve. This unit comes with or without foot pedal.



CE EN 15154

Standard Fixtures:

- Shower Bowl:**
 - 280mm (11") bowl is injection moulded in chemical resistant polycarbonate in bright yellow colour with stainless steel outlet.
- Eyewash Assembly:**
 - Stainless Steel with polycarbonate sprayheads assembly with twin, soft-flow eyewash heads and instant flip-open protective dust cover. The built in automatic pressure compensating valve assures safe steady flow under varying water supply conditions. Sprayheads also include a filter to protect user against particles from the water flow which may be damaging to the eyes and face.
- Control Valve:**
 - 1 ¼" fast action stainless-steel ball valve is used for the shower assembly with the stainless steel pull rod.
 - ½" fast-action stainless steel ball valve is used for the eyewash assembly with stainless steel push plate.
- Pedestal:**
 - 250mm (10") aluminium pedestal with 3 mounting holes 9mm bolts. Pedestal is brightly powder coated in yellow.
- Pipe and Fittings:**
 - 1 ¼" IPS stainless steel pipe epoxy powder coated with bright safety yellow colour.
- Waste:**
 - 1 ¼" IPS
- Water Supply:**
 - 1 ¼" IPS
- Signage:**
 - Drench Shower and Eyewash
- Compliance:**
 - EN 15154-2:2006, EN 15154-5:2019
- Pipe Threads:**
 - Pipe threads in accordance to BS 21 or DIN 259 are supplied as standards. NPT pipe threads are also available upon request.

Material List

N.O	Material	Specifications
1	Shower Bowl	304 SS/PC
2	1 ¼" IPS Supply	304 Stainless Steel
3	Pipe/ T Pipe	304 Stainless Steel
4	1 ¼" Ball Valve	304 Stainless Steel
5	Lever	304 SS 6" bent
6	Pull Rod	304 SS 700 mm
7	U-Bent Pipe	304 SS
8	Foot Pedal	250 mm Aluminium Injected Plate
9	Bolt Screw-Floor Stand	9mm Diameter Screw 10" Aluminium Injected Plate
10	Chain	304 SS
11	Eyewash Bowl	304 SS/PC
12	Triangle Signage	PC

PROGUARD TECHNOLOGIES (M) SDN. BHD. (258964-U)

T +603 9021 3233 (Hunting Line) F +603 9021 3133/ 9021 2733
E proguard@proguardsafety.com
Lot 408 & 409, Jalan Sungai Tekali, 43100 Hulu Langat, Selangor, Malaysia.

EAST COAST Branch :

T +609 567 5989/ 568 5989 F +609 568 9889
E proguardseastcoast@proguardsafety.com
A-61, Jalan Seri Setali 2, Off Jalan Air Putih, 25300 Kuantan, Pahang, Malaysia.

SUBANG JAYA Branch :

T +603 5192 8788 F +603 5192 1788 E pgsj@proguardsafety.com
No.10, Jalan Putra Mahkota 7/6B,
47650 Putra Heights, Subang Jaya, Selangor, Malaysia.

SOUTHERN Branch :

T +607 353 0780 (Hunting Line) F +607 354 9086
E proguardsouthern@proguardsafety.com
6, Jalan Molek 2/5, Taman Molek, 81100 Johor Bharu, Johor, Malaysia.

MELAKA Branch :

T +606 335 4552 (Hunting Line) F +606 335 4557
E pgmelaka@proguardsafety.com
No.7 & 7-1, Jalan MP3, Taman Merdeka Permai, 75350 Melaka, Malaysia.

EAST MALAYSIA Branch :

T +6085 430888/+6085 437888/+6085 417888 (Hunting Line)
F +085 435 886 E pgem@proguardsafety.com
Lot 1830 & 1831, Eastwood Valley Industrial Park Phase 3,
Miri By Pass Road, 98000 Miri, Sarawak, Malaysia.

PROGUARD SAFETY (NORTHERN) SDN. BHD. (592968-H)

T +604 288 8181 (Hunting Line) F +604 288 8188/ 288 8189
E proguardnorthern@proguardsafety.com
13-G, 13-1, 13-2, Vantage Point, Jalan Lenggong, 11600 Jelutong, Penang, Malaysia.

SRI MANJUNG Branch :


T +605 688 7348 (Hunting Line) F +605 688 7343
E pgsrm@proguardsafety.com
13, Persiaran PM 3/2, Pusat Bandar Sekysen 3, 32040 Sri Manjung, Perak, Malaysia.



TECHNICAL DATA

Polycarbonate Bowl Combination Emergency Shower & Eyewash |
 Polycarbonate Bowl Combination Emergency Shower &
 Eyewash with Foot Pedal
 Model: PG 10020 AB | PG 10022 AB

PROGUARD[®]
 Your Ultimate Partner In Safety[®]



UNIT: mm/"Inch

VARIANCE: 0.05

Product Code	Description	Packing
PG 10020 AB	Polycarbonate Bowl Combination Emergency Shower & Eyewash	1 unit / ctn
PG 10022 AB	Polycarbonate Bowl Combination Emergency Shower & Eyewash with Foot Pedal	1 unit / ctn

PROGUARD TECHNOLOGIES (M) SDN. BHD. (258964-U)
 T +603 9021 3233 (Hunting Line) F +603 9021 3133/ 9021 2733
 E proguard@proguardsafety.com
 Lot 408 & 409, Jalan Sungai Tekali, 43100 Hulu Langat, Selangor, Malaysia.

EAST COAST Branch :
 T +609 567 5989/+6085 437 886 F +609 568 9889
 E proguardeastcoast@proguardsafety.com
 A-61, Jalan Seri Setali 2, Off Jalan Air Putih, 25300 Kuantan, Pahang, Malaysia.

SUBANG JAYA Branch :
 T +603 5192 8788 F +603 5192 1788 E pgsj@proguardsafety.com
 No.10, Jalan Putra Mahkota 7/68,
 47650 Putra Heights, Subang Jaya, Selangor, Malaysia.

SOUTHERN Branch :
 T +607 353 0780 (Hunting Line) F +607 354 9086
 E proguardsouthern@proguardsafety.com
 6, Jalan Molek 2/5, Taman Molek, 81100 Johor Bharu, Johor, Malaysia.

PROGUARD SAFETY (NORTHERN) SDN. BHD. (592968-H)
 T +604 288 8181 (Hunting Line) F +604 288 8188/ 288 8189
 E proguardnorthern@proguardsafety.com
 13-G, 13-1, 13-2, Vantage Point, Jalan Lenggong, 11600 Jelutong, Penang, Malaysia.

MELAKA Branch :
 T +606 335 4552 (Hunting Line) F +606 335 4557
 E pgmelaka@proguardsafety.com
 No.7 & 7-1, Jalan MP3, Taman Merdeka Permai, 75350 Melaka, Malaysia.

EAST MALAYSIA Branch :
 T +6085 430 886/+6085 437 886/+6085 417 886 (Hunting Line)
 F +085 435 886 E pgem@proguardsafety.com
 Lot 1830 & 1831, Eastwood Valley Industrial Park Phase 3,
 Miri By Pass Road, 98000 Miri, Sarawak, Malaysia.

SRI MANJUNG Branch :
 T +605 688 7348 (Hunting Line) F +605 688 7343
 E pgsrm@proguardsafety.com
 13, Persiaran PM 3/2, Pusat Bandar Sekyren 3, 32040 Sri Manjung, Perak, Malaysia.



TECHNICAL DATA

Polycarbonate Bowl Combination Emergency Shower & Eyewash |
Polycarbonate Bowl Combination Emergency Shower &
Eyewash with Foot Pedal
Model: PG 10020 AB | PG 10022 AB

PROGUARD[®]
Your Ultimate Partner In Safety[®]



PG 10020 AB



PG 10022 AB

PROGUARD TECHNOLOGIES (M) SDN. BHD. (258964-U)

T +603 9021 3233 (Hunting Line) F +603 9021 3133/ 9021 2733
E proguard@proguardsafety.com
Lot 408 & 409, Jalan Sungai Tekali, 43100 Hulu Langat, Selangor, Malaysia.

SUBANG JAYA Branch :

T +603 5192 8788 F +603 5192 1788 E pgsj@proguardsafety.com
No.10, Jalan Putra Mahkota 7/68,
47650 Putra Heights, Subang Jaya, Selangor, Malaysia.

MELAKA Branch :

T +606 335 4552 (Hunting Line) F +606 335 4557
E pgmelaka@proguardsafety.com
No.7 & 7-1, Jalan MP3, Taman Merdeka Permai, 75350 Melaka, Malaysia.

EAST COAST Branch :

T +609 567 5989/ 568 5989 F +609 568 9989
E proguardseastcoast@proguardsafety.com
A-61, Jalan Seri Setali 2, Off Jalan Air Putih, 25300 Kuantan, Pahang, Malaysia.

SOUTHERN Branch :

T +607 353 0780 (Hunting Line) F +607 354 9086
E proguardsouthern@proguardsafety.com
6, Jalan Molek 2/5, Taman Molek, 81100 Johor Bharu, Johor, Malaysia.

EAST MALAYSIA Branch :

T +6085 430886 / +6085 437886 / +6085 417886 (Hunting Line)
F +085 435 886 E pgem@proguardsafety.com
Lot 1830 & 1831, Eastwood Valley Industrial Park Phase 3,
Miri By Pass Road, 98000 Miri, Sarawak, Malaysia.

PROGUARD SAFETY (NORTHERN) SDN. BHD. (592968-H)

T +604 288 8181 (Hunting Line) F +604 288 8188/ 288 8189
E proguardnorthern@proguardsafety.com
13-G, 13-1, 13-2, Vantage Point, Jalan Lenggong, 11600 Jelutong, Penang, Malaysia.

SRI MANJUNG Branch :

T +605 688 7348 (Hunting Line) F +605 688 7343
E pgsm@proguardsafety.com
13, Persiaran PM 3/2, Pusat Bandar Seksyen 3, 32040 Sri Manjung, Perak, Malaysia.

