



Part Number : [512385011](#)
Product Description : CRC Shielded Rectangular I/O Receptacle Housing for Female Terminal, Signal, 50 Circuits, Polarization Type Standard
Series Number : 51238
Status : Active
Product Category : I/O Connectors



Documents & Resources


Drawings
[512385011_sd.pdf](#)

3D Models and Design Files
[512385011_stp.zip](#)

Specifications
[AS-51238-017-001.pdf](#)
[PS-51238-016-001.pdf](#)
[PS-51238-017-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	I/O Connectors
Series	51238
Description	CRC Shielded Rectangular I/O Receptacle Housing for Female Terminal, Signal, 50 Circuits, Polarization Type Standard
Application	Panel-Mount, Wire-to-Wire
Component Type	Housing
Product Name	CRC
Type	N/A
UPC	756054154700

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.5A, 1.0A, 2.5A, 2.0A
Shielded	No
Voltage - Maximum	250V AC (RMS)/DC

Physical

Circuits (Loaded)	50
Circuits (maximum)	50
Color - Resin	Gray
Durability (mating cycles max)	100

Flammability	94V-0
Gender	Receptacle
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Stainless Steel
Material - Plating Mating	N/A
Material - Resin	Polyester
Net Weight	8679.900/mg
Number of Rows	10
Orientation	Vertical
Packaging Type	Tray
Panel Mount	Front, Rear
PCB Locator	No
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Polarized to PCB	N/A
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	N/A
Waterproof / Dustproof	No

Mates With / Use With

Mates with Part(s)

Description	Part Number
CRC Shielded Rectangular I/O Plug Housings	<u>51234</u>
CRC Shielded Rectangular I/O Plug Assembly Sets	<u>55836</u>

Use with Part(s)

Description	Part Number
CRC Signal Female Terminals	<u>56120</u>
CRC Signal Female Terminals	<u>56121</u>
CRC Shielded Rectangular I/O Receptacle Shells	<u>56377</u>

This document was generated on Apr 22, 2025