

# TRICOTRIL® WINTER 739



## APPLICATION:

- Working in cold areas
- Working in areas with momentary steam hazard
- Handling of contaminated heavy parts
- Cleaning and maintenance in chemical plants
- Galvanising works
- Chemical industry

## QUALITIES AND ADVANTAGES:

- Insulating effect at high or low temperatures
- Short-term cold protection down to -20 °C
- Broad chemical resistance
- High mechanical resistance
- Good grip when handling greasy and oily parts
- High user comfort for long working periods without operator fatigue

## FEATURES:

- AQL < 0,65
- Free from natural latex
- Warming seamless wool liner
- Skin friendly by solvent-free adhesive on the wool liner
- Wool liner is fixed later to the finished glove to ensure maximum protection
- Food safety according to EU 1935/2004

| ATTRIBUTE              | DESCRIPTION / VALUES                                                                                                                                                                                                                                                      |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article No.<br>Name    | <ul style="list-style-type: none"><li>• 739</li><li>• Tricotril® Winter 739</li></ul>                                                                                                                                                                                     |
| Material               | <ul style="list-style-type: none"><li>• Nitrile</li><li>• Wool</li></ul>                                                                                                                                                                                                  |
| Description            | <ul style="list-style-type: none"><li>• Heavy seamless wool liner,</li><li>• Cuff, fully coated,</li><li>• Palm profile</li></ul>                                                                                                                                         |
| Length (mm)            | <ul style="list-style-type: none"><li>• 390 - 410</li></ul>                                                                                                                                                                                                               |
| Total thickness (mm)   | <ul style="list-style-type: none"><li>• 2,0 ± 0,2</li></ul>                                                                                                                                                                                                               |
| Coating thickness (mm) | <ul style="list-style-type: none"><li>• 0,4</li></ul>                                                                                                                                                                                                                     |
| Colour                 | <ul style="list-style-type: none"><li>• Green</li></ul>                                                                                                                                                                                                                   |
| Size                   | <ul style="list-style-type: none"><li>• 8, 9, 10, 11</li></ul>                                                                                                                                                                                                            |
| Classification         | <ul style="list-style-type: none"><li>• Category III</li></ul> <div><div>EN 388:2016</div><div>EN 374-1/Type A</div><div>EN 374</div><div>EN 407</div><div>EN 511</div><div></div><div>3121X</div><div>AJKLOPT</div><div>Virus</div><div>X1XXXX</div><div>X11</div></div> |



CHEMICAL PROTECTIVE GLOVES

## HONEYWELL PPE KCL GmbH

Industriepark Rhoen  
Am Kreuzacker 9  
36124 Eichenzell, Germany  
Phone: +49 69 80885425  
[kclorders@honeywell.com](mailto:kclorders@honeywell.com)  
[sps.honeywell.com](https://sps.honeywell.com)

Honeywell KCL Tricotril Data Sheet - 01/2023  
© 2023 Honeywell International Inc.

# Honeywell

