

CABLE-25/8/250/PSR-M/001/R - Adapter cable



1574602

<https://www.phoenixcontact.com/gb/products/1574602>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable adapter for PSRmodular (PSR-M-EM...), 25/8-pos., cable entry on the right, cable length 2.5 m



Commercial data

Item number	1574602
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DNA366
Product key	DNA366
GTIN	4067923064218
Weight per piece (including packing)	187.7 g
Weight per piece (excluding packing)	187 g
Customs tariff number	85444290
Country of origin	IT

CABLE-25/8/250/PSR-M/001/R - Adapter cable



1574602

<https://www.phoenixcontact.com/gb/products/1574602>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Adapter cable
--------------	---------------

Connection data

To the device

Connection method	RJ45
-------------------	------

Encoder / PLC

Connection method	D-SUB-25 male/D-SUB-25 female
Number of positions	25

Material specifications

Outer sheath, material	PVC
Conductor material	Bare Cu litz wires

Cable/line

Cable length	2.5 m
Outer sheath, material	PVC
External sheath, color	green (RAL 6016)
Cable cross section	0.48 mm ² (AWG 26)
Conductor material	Bare Cu litz wires
Shielding	Plastic-coated aluminum foil, tinned copper braided shield
	Soldering on D-SUB housing
Cable resistance	≤ 144 Ω/km (Loop)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C (for fixed installation)
Ambient temperature (storage/transport)	-30 °C ... 80 °C


CABLE-25/8/250/PSR-M/001/R - Adapter cable

1574602

<https://www.phoenixcontact.com/gb/products/1574602>

Drawings

Schematic diagram



CABLE-25/8/250/PSR-M/001/R - Adapter cable



1574602

<https://www.phoenixcontact.com/gb/products/1574602>

Classifications

ECLASS

ECLASS-13.0	27371390
-------------	----------

ETIM

ETIM 9.0	EC002498
----------	----------

CABLE-25/8/250/PSR-M/001/R - Adapter cable



1574602

<https://www.phoenixcontact.com/gb/products/1574602>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk