



TE DISPENSING TIPS



Features a stainless steel cannula with double Helix polypropylene hub. The burr free electro polished cannula provides unobstructed flow and consistent fluid flow. Pack of 50.

Gauge	¼"/6.35mm	½"/12.7mm	1"/25.4mm	1.5"/38.1mm
14		TE714050PK	TE714100PK	TE714150PK
15		TE715050PK	TE715100PK	TE715150PK
18	TE718025PK	TE718050PK	TE718100PK	TE718150PK
20	TE720025PK	TE720050PK	TE720100PK	TE720150PK
21	TE721025PK	TE721050PK	TE721100PK	TE721150PK
22	TE722025PK	TE722050PK	TE722100PK	TE722150PK
23	TE723025PK	TE723050PK	TE723100PK	TE723150PK
25	TE725025PK	TE725050PK	TE725100PK	
27	TE727025PK	TE727050PK	TE727100PK	
30	TE730025PK	TE730050PK	TE730100PK	
32	TE732025PK			
34	TE734025PK			

TE BENT DISPENSING TIPS



Features all the same advantages as the standard TE tip but with preset bends in the cannula, for difficult to reach areas. Pack of 50.

Gauge	90° ½"/6.35mm	45° ¼"/12.7mm	45° 1.5"/38.1mm
14	TE714050B90PK	TE714050B45PK	TE714150B45PK
15	TE715050B90PK	TE715050B45PK	
18	TE718050B90PK	TE718050B45PK	TE718150B45PK
20	TE720050B90PK	TE720050B45PK	
21	TE721050B90PK	TE721050B45PK	TE721150B45PK
22	TE722050B90PK	TE722050B45PK	
23	TE723050B90PK	TE723050B45PK	
25	TE725050B90PK	TE725050B45PK	
27	TE727050B90PK	TE727050B45PK	
30	TE730050B90PK	TE730050B45PK	


TT TAPERED DISPENSING TIPS



Tapered tips prevent blockages and increase fluid flow rates with high viscosity fluids. Standard tips made from HD polyethylene with UV light block additive. Rigid tips made from polypropylene with opaque color. Pack of 50.

Gauge	Standard	Rigid
14	TT14DHUV-PK	TT14-RIGID-PK
16	TT16DHUV-PK	TT16-RIGID-PK
18	TT18DHUV-PK	TT18-RIGID-PK
20	TT20DHUV-PK	TT20-RIGID-PK
22	TT22DHUV-PK	TT22-RIGID-PK
25	TT25DHUV-PK	TT25-RIGID-PK
27	TT27DHUV-PK	TT27-RIGID-PK

TEFLON® LINED DISPENSING TIPS



Use with low viscosity fluids and CA's (Cyanoacrylates). Resists clogging and prevents damage to substrate. Lined with Teflon® which is crimped inside the cannula. Pack of 50.

Gauge	½"/12.7mm	1"/25.4mm
20	TF720050PK	TF720100PK
25	TF725050PK	TF725100PK

BT BRUSH DISPENSING TIPS



Brush tips spread fluid evenly. Soft bristles made from Red Sable and stiff bristles made from Nylon. Pack of 12.

Gauge	Soft Bristle	Stiff Bristle
16	BT16-SOFTPK	BT16-SOFTPK
18	BT18-SOFTPK	BT18-SOFTPK
22	BT22-SOFTPK	BT22-SOFTPK

TS-P FLEXIBLE DISPENSING TIPS



Flexible tips allow access to hard to reach areas. The flexible cannula allows the user to "customise" the length. Made from polypropylene. Pack of 50.

Gauge	1.5"/38.1mm
15	TS15P-1-1/2PK
16	TS16P-1-1/2PK
18	TS18P-1-1/2PK
20	TS20P-1-1/2PK
22	TS22P-1-1/2PK
25	TS25P-1-1/2PK