

## Features

- Electrical control with touch button
- 3 speeds
- 3 wind modes: Normal, Natural & Sleep
- 12H timer
- Quiet operation
- Overheat protective motor
- Automatic oscillation up to 85°
- Remote control

## RS PRO Tower Fan 23.07m<sup>3</sup>/min, 3 speed 220-240V, with Type G -British 3-pin

RS Stock No.: 0735032



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### RS PRO Tower Fan

Keep your space cool, fresh, and comfortable with the RS PRO Tower Fan. This whisper-quiet fan has 3-speed control settings that you can easily adjust using the remote control. The timer feature lets you set it for up to 12 hours. Get ready for some cool relief.

### Features and Benefits

- Electrical control with touch button
- 3 speeds
- 3 wind modes for normal, natural & sleep
- Automatic oscillation up to 85°
- 12 hours timer
- With remote control
- Overheat protective motor

## General Specifications

<b>Air Flow</b>	23.07 m <sup>3</sup> /min
<b>Fan Type</b>	Tower
<b>Number of Speeds</b>	3
<b>Plug Type</b>	Type G – British 3-pin
<b>Supply Voltage</b>	220-240 V
<b>Dimensions</b>	240 x 240 x 765 mm
<b>Height</b>	765mm
<b>Special Features</b>	Oscillating
<b>Noise Level</b>	<39dB(1 <sup>st</sup> setting); <46dB(2 <sup>nd</sup> setting); <58.6dB(3 <sup>rd</sup> setting)

## Electrical Specifications

<b>Rated Voltage</b>	220-240V
<b>Rated Frequency</b>	50/60Hz
<b>Rating Power</b>	45W
<b>Airflow</b>	1350 rpm
<b>Swinging Head Angle</b>	85°
<b>Weight (G.W)</b>	2.4kgs

## Approvals

<b>Declaration</b>	REACH DoC
<b>Certifications</b>	CE, GS
<b>Standards Meet</b>	EN 60335-2-80:2003+A1:2004+A2:2009 EN 60335-1:2012+A11:2014+A13:2017 A1:2019+A14:2019+A2:2019+A15:2021+ A16:2023 EN 62233: 2008

## Similar Products

Stock No.	Brand	Product Name	No of Speed	Timmer	Plug Type
227-903	RS PRO	Tower Fan	3 speeds	8 hours	Type G – British 3-pin
227-904	RS PRO	Tower Fan	3 speeds	8 hours	Type C – European Plug