

HC-B 16-ANDOCK - Docking frame

1586138

<https://www.phoenixcontact.com/gb/products/1586138>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Docking frame for racks, for contact inserts of B16 type, with four M5 flat headed screws, rack balance x/y axis ± 1.5 mm

Commercial data

Item number	1586138
Packing unit	2 pc
Minimum order quantity	2 pc
Sales key	AF7AZB
Product key	AF7AZB
Catalog page	Page 663 (C-2-2019)
GTIN	4046356345729
Weight per piece (including packing)	109.75 g
Weight per piece (excluding packing)	50 g
Customs tariff number	85389099
Country of origin	CN

HC-B 16-ANDOCK - Docking frame

1586138

<https://www.phoenixcontact.com/gb/products/1586138>




Technical data

Product properties

Product type	Docking frame
Type	B16
Number of module slots	4

Dimensions

Dimensional drawing	
Width	55 mm
Height	119.5 mm
Depth	25.8 mm

Material specifications

Material	Stainless steel
----------	-----------------

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 125 °C

Mounting

Assembly note	For contact inserts from series B16, D40, DD72, BB32, BBB40, K, M
---------------	---

HC-B 16-ANDOCK - Docking frame


1586138

<https://www.phoenixcontact.com/gb/products/1586138>



Drawings

Dimensional drawing



Dimensional drawing


HC-B 16-ANDOCK - Docking frame

1586138

<https://www.phoenixcontact.com/gb/products/1586138>




Dimensional drawing



Mounting cutout

Dimensional drawing



max. dimensions of both the docking frames (in case of standard contacts 25.8 mm; in case of fiber optics contacts 27 mm; in case of pneumatic contacts 26.5 mm)

HC-B 16-ANDOCK - Docking frame



1586138

<https://www.phoenixcontact.com/gb/products/1586138>

Classifications

ECLASS

ECLASS-13.0	27440206
-------------	----------

ETIM

ETIM 9.0	EC002312
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-B 16-ANDOCK - Docking frame



1586138

<https://www.phoenixcontact.com/gb/products/1586138>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk