



Cut



Oil

Ergonomic Protection



Medium Duty

## Medium-duty work gloves, ensuring secure grip and abrasion, cut and oil protection

- **Heightened durability:** Featuring a fully NBR-coated seamless liner with a rough palm, EDGE<sup>®</sup> 48-929 protective gloves offer a highly secure grip in oily environments, while protecting skin from injuries and oil contamination
- **Specialized protection:** Tested and certified under EN 420 (general requirements) and EN 388 (mechanical hazards), these cost-effective nitrile gloves offer excellent resistance to abrasions, cuts and oils
- **Enhanced features:** EDGE<sup>®</sup> 48-929 hand protection gloves' elastic knitwrist grants a secure and snug fit around the wrist, making them ideal for workers handling small and medium-sized sharp components coated with oils or lubricants
- **Food handling compliance:** In addition, these food gloves comply with FDA food handling requirements and the Commission Regulation (EC) No. 1935/2004 as well as the Regulation (EC) No. 2023/2006 related to Good Manufacturing Practices (GMP) for materials and articles intended to come in contact with foodstuffs



### Industries

- Aerospace
- Automotive
- Glass manufacturing
- Machinery and Equipment
- Metal fabrication
- Transportation
- Chemical
- Oil and gas
- Food Processing

### Applications

- Machining / Stamping / Cutting
- Grinding
- Assembly of parts
- Maintenance
- Handling of glass sheets, sharp edged objects
- Handling materials with sharp or rough edges
- Handling sharp metal or objects
- Food Processing

### Key Features

- **NBR coating:** For safety gloves with superior grip and skin protection
- **EN 420- and EN 388-certified:** Protect against mechanical hazards
- **Elastic knitwrist:** For enhanced wrist protection and comfort

### Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X43C



### Specifications

| BRAND   STYLE            | DESCRIPTION                                                                                                                                                     | Gauge | SIZE                   | LENGTH                        | COATING COLOR | PACKAGE                      |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|------------------------|-------------------------------|---------------|------------------------------|
| EDGE <sup>®</sup> 48-929 | <b>Finishing:</b> Fully Dipped<br><b>Coating Material:</b> Nitrile<br><b>Liner Material:</b> Spandex, Fiber glass, Polyethylene<br><b>Cuff Style:</b> Knitwrist | 13    | 6, 7, 8, 9, 10, 11, 12 | 225-285 mm, 8.89-11.22 inches | Black         | 12 pairs/bag, 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, <sup>®</sup> and <sup>™</sup> are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.