



BU-00000-\*  
Part # color

\* 0 - Black 5 - Green  
2 - Red 6 - Blue  
4 - Yellow 9 - White

TEST LEADS

1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 Page 5

#### BU-1481-E-00-\*

##### "Mini-Micro-Plunger" To 0.025" (0.6 mm) Square Pin

- No. 208 gold-plated one-piece beryllium copper conductor.
- Nylon stem and cap and stainless steel compression string.
- Attaches to 0.025" (.6mm) dia. and smaller component leads.
- Square Pin has gold-plated alloy 360 copper insert with ABS housing.
- #22 AWG wire (19/34) tinned copper with 105°C PVC insulation.
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



#### BU-2020-A-00-\*

##### Stackable Single Banana Plug— Both Ends

- Nine-leaf beryllium copper, nickel-plated spring.
- Double stacking ability.
- #20 AWG wire (41/36) tinned copper with 105°C PVC insulation.
- [Product Data Sheet & Compatibility Info](#)
- [Send us your questions about this product](#)



Enlarge

#### BU-2030-A-00-\*

##### Insulated Alligator Clip To Stackable Banana Plug

- Nickel-plated steel with PVC insulator; jaw opens to 5/16" (7.9 mm).
- Nine-leaf beryllium copper, nickel-plated spring.
- Double stacking ability.
- #20 AWG (41/36) tinned copper wire with 105°C PVC insulation.
- [Product Data Sheet & Compatibility Info](#)
- [Send us your questions about this product](#)



Click for Larger Image

#### BU-2031-A-00-\*

##### Insulated Mini-Alligator Clip To Stackable Banana Plug

- Nickel-plated steel with durable PVC insulator.
- Jaw opens to 3/16" (4.7 mm).
- Nine-leaf beryllium copper, nickel-plated spring.
- #20 AWG wire (41/36) tinned copper with 105°C PVC insulation.
- [Product Data Sheet & Compatibility Info](#)
- [Send us your questions about this product](#)



[Contents](#)|[Next](#)

[Home](#)|[Insulated BNCs](#)|[Clips & Insulators](#)|[Insulated Test Accessories](#)  
[Accessories & Probes](#)|[Kits](#)|[Cross Reference](#)

©1999-2000 Mueller Electric Company. All rights reserved.  
Problems with the site should be reported to the [webmaster](#).