



BOA FLEX

EN ISO 21420 : 2020



CAT. II

EN 388



4 1 3 1 A

EN 407



X 1 X X X X



EN 388 : 2016 +A1 : 2018

• ABRASION	: 4/4
• BLADE CUT	: 1/5
• TEARING	: 3/4
• PERFORATION	: 1/4
• CUTTING BY SHARP OBJECT (ISO 13997)	: A/F

EN 407 : 2020

• FIRE BEHAVIOR	: X/4
• CONTACT HEAT	: 1/4
• CONVECTIVE HEAT	: X/4
• RADIANT HEAT	: X/4
• SMALL SPLASHES OF LIQUID METAL	: X/4
• LARGE SPLASHES OF LIQUID METAL	: X/4



ISO 6330

FEATURES

- GREY NYLON/SPANDEX/ELASTHANE KNIT GLOVES
- 15 GAUGE
- BLACK NITRILE MICROFOAM COATING

RECOMMENDED USES

- AUTOMOTIVE ASSEMBLY
- LOGISTICS AND WAREHOUSING
- FINISHING AND INSPECTION

AVAILABLE SIZES



CE MARKING

- THIS MARKING SIGNIFIES COMPLIANCE WITH THE ESSENTIAL REQUIREMENTS PROVIDED FOR BY EUROPEAN REGULATION 2016/425, RELATING TO PERSONAL PROTECTIVE EQUIPMENT

SAFETY, COMFORT, AND DEXTERITY

- DEXTERITY: LEVEL 5
- THIS GLOVE DOES NOT CONTAIN ANY SUBSTANCE AT SUCH LEVELS AS TO BE KNOWN OR SUSPECTED OF HAVING ADVERSE EFFECTS ON THE HYGIENE OR HEALTH OF THE USER UNDER THE EXPECTED CONDITIONS OF USE



PRECAUTIONS FOR USE

- WEAR GLOVES ON CLEAN, DRY HANDS
- IT IS RECOMMENDED TO CARRY OUT A PRELIMINARY TEST UNDER REAL CONDITIONS OF USE, WHICH MAY DIFFER FROM EU TYPE TESTING
- BEFORE RE-USE, CHECK GLOVES FOR DEFECTS, HOLES, TEARS, ABNORMAL WEAR, ETC

STORAGE AND MAINTENANCE

- STORE PRODUCTS IN A DRY, COOL, WELL-VENTILATED PLACE, AWAY FROM LIGHT, SUNLIGHT AND ULTRAVIOLET RAYS, AND IN THEIR ORIGINAL PACKAGING
- WHEN CORRECTLY STORED, GLOVES RETAIN THEIR PROPERTIES WITHOUT UNDERGOING SIGNIFICANT CHANGE
- NO SPECIAL MAINTENANCE REQUIRED
- MACHINE WASHABLE ON 3 CYCLES

PACKAGING

- IN CASE OF DECONDITIONING, A COPY OF THE NOTICE MUST BE ENCLOSED WITH THE SMALLEST PACKAGING
- BAG OF 10 PAIRS
- BOX OF 100 PAIRS

LIMITATIONS OF PROTECTION

- DO NOT USE FOR HANDLING OBJECTS AT TEMPERATURES OVER 100°C
- DO NOT USE FOR HANDLING CHEMICALS OR LIQUIDS

DISPOSAL

- END-OF-LIFE DESTRUCTION MUST BE CONTROLLED AND COMPLY WITH EUROPEAN TRACEABILITY AND ENVIRONMENTAL REQUIREMENTS

EU TYPE CERTIFICATE ISSUED IN ACCORDANCE WITH MODULE B REGULATION (EU) 2016/425 - SATRA N°: 2777

THE EU DECLARATION OF CONFORMITY IS AVAILABLE ON REQUEST. CONTACT US VIA OUR WEBSITE WWW.GUYARD-SA.COM, "CONTACT" SECTION

GUYARD SAS 22-24, RUE LUCIEN ROUZET
Z.A. VILLEDIEU SUR INDRE/NIHERNE
36250 NIHERNE FRANCE

TEL. +33 (0)2 54 35 63 70
E-MAIL :CONTACTS@GUYARD-SA.COM
S.A.S AU CAPITAL DE 1 150 000€ | SIRET 341 274 876 00034
CODE APE 4642Z | TVA INTRA : FR 19 341 274 876