

IBM PC Compatible I/O brackets

I/O Card Brackets

IBM brackets are available in various forms, with or without board fixing 'ears' with provision for different types of connector I/O, and are designed for fitting on either the component or solder side of the board. 20 bracket types are available ex-stock covering the most widely used applications. All brackets are manufactured from 0,80mm thick steel and finished in bright nickel plate.

I/O card brackets for IBM PC, PCXT and PCAT			Ordering information
Type	Description	PCB mtg. ctrs.	Order code
A	25 way "D"-Sub type	-	427-59693
B	9 way "D"-Sub type	-	427-59692
C	Twin phone type	73,7mm	427-59694
D	15 way "D"-Sub type	-	427-59695
E	37 way "D"-Sub type	-	427-59696
F	9 way & 25 way "D"-Sub type	-	427-59697
H	Blank panel: component side mounted	61,0mm	427-59699
J	Blank panel: no PCB mounting	-	427-59700
K	Blank panel: solder side mounted	88,9mm	427-59701
L	Blank panel: component side mounted	88,9mm	427-59702
M	37 way "D"-Sub type: solder side mounted	90,8mm	427-59703
N	Blank panel: solder side mounted	90,8mm	427-10036
P	50 way "D"-Sub type	-	427-10023
AA	15 way & 15 way "D"-Sub type	-	427-10027
BA	15 way & 25 way "D"-Sub type	-	427-10037
CA	15 way "D"-Sub type & BNC 12,8mm	-	427-10038
DA	25 way "D" type: solder side mounted	90,8mm	427-10039
EA	50 way Centronics	-	427-10040
FA	9 way "D"-Sub type: solder side mounted	90,8mm	427-10032
GA	9 way & 9 way "D"-Sub type	-	427-10041


Note: Fixing screws for I/O brackets with board fixing ears are available in packs of 100

Order code	427-56169
-------------------	------------------


PCI I/O Card brackets

To support the PCI products that are being introduced into the marketplace, APW is offering a range of PCI brackets. Nine brackets are available to cover the most widely used applications, and all brackets are manufactured from 0,80mm thick steel and finished in bright nickel plate.

PCI I/O Card Brackets			Ordering information
Type	Description	PCB mtg. ctrs	Order code
J	Blank bracket - no PCB mounting	-	427-59700
AB	25 way 'D' cut-out - no PCB mounting	-	427-314431
BB	9 way 'D' cut-out - no PCB mounting	-	427-314432
CB	Blank bracket - PCB mounting	85,39 mm	427-314433
DB	Blank bracket - with 4-40 PCB mounting	85,39 mm	427-314434
EB	Blank bracket - with M3 PCB mounting	85,39 mm	427-314435
FB	9 way 'D' cut-out - with 4-40 PCB mounting	85,39 mm	427-314436
GB	25 way 'D' cut-out - with 4-40 PCB mounting	85,39 mm	427-314437
HB	9 way 'D' cut-out - with 4-40 PCB mounting	85,39 mm	427-314438



IBM PC I/O Card brackets



PCI I/O Card brackets