

URTK/S GEHAEUSE - Housing



5026869

<https://www.phoenixcontact.com/gb/products/5026869>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Housing



Commercial data

Item number	5026869
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	ACEDAB
Product key	ACEPAA
GTIN	4017918245627
Weight per piece (including packing)	8.634 g
Weight per piece (excluding packing)	8.37 g
Customs tariff number	85472000
Country of origin	CN

URTK/S GEHAEUSE - Housing



5026869

<https://www.phoenixcontact.com/gb/products/5026869>

Technical data

Product properties

Product type	Housing
Product family	Plastic

Connection data

Cable lug connection

Cross section range AWG	(converted acc. to IEC)
-------------------------	-------------------------

Material specifications

Color (Housing)	gray (RAL 7042)
Color of the housing part	gray
Material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	27,5 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

URTK/S GEHAEUSE - Housing



5026869

<https://www.phoenixcontact.com/gb/products/5026869>

Classifications

ECLASS

ECLASS-13.0	27440202
-------------	----------

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

URTK/S GEHAEUSE - Housing

5026869

<https://www.phoenixcontact.com/gb/products/5026869>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk