



1607

Air

Peli™ Air cases are the first in a series of remarkable innovations engineered by Peli, the pioneers of protective cases. For over 45 years Peli has designed and crafted the most influential protective cases in the world, and we're just getting started. With the launch of the Peli™ Air line of cases, we're redefining the future of protection with a remarkable union of light and tough.

- Automatic pressure equalization valve - balances interior pressure, keeps water out
- Fold down over-molded handle
- Retractable extension trolley handle
- Stainless steel padlock protectors
- Business card holder
- Quiet rolling stainless-steel bearing wheels
- Press and Pull™ Latches
- Limited Lifetime Warranty
- Super-light proprietary HPX²™ Polymer - up to 40% lighter
- Waterproof O-ring seal
- User-customizable Pick N Pluck™ foam
- Waterproof, crushproof, dustproof
- IP67 & MIL-SPEC certified



CONFIGURATIONS



1607
Standard



1607NF
No Foam



1607WD
With Padded Dividers



1607WF
With Foam

DIMENSIONS

Interior (L×W×D)	21.05 x 15.81" x 11.63 (53.5 x 40.2 x 29.5 cm)
Exterior (L×W×D)	24.13 x 18.80" x 13.25 (61.3 x 47.8 x 33.7 cm)
Lid Depth	2.00" (5.1 cm)
Bottom Depth	9.60" (24.4 cm)
Total Depth	11.6" (29.5 cm)
Int Volume	2.24 ft ³ (0.063 m ³)
Padlock Hole Diameter	0.31" (0.8 cm)

MATERIALS

Body	Proprietary Polypropylene Blend
Latch	ABS
O-Ring	EPDM
Purge Body	ABS

Purge Vent

Hi-Flow Gore-Tex 3 Micron Hydrophobic Non-Woven

COLOURS Black Orange Silver Yellow**WEIGHT**

Weight With Foam	16.10 lbs (7.3 kg)
Weight Empty	13.20 lbs (6 kg)
Buoyancy	178.00 lbs (80.7 kg)

TEMPERATURE

Minimum Temperature	-60°F (-51.1 °C)
Maximum Temperature	160°F (71.1 °C)

OTHER

Wheels	2
---------------	---

ACCESSORIES

1506TSA
TSA Lock



1500D
Desiccant Silica Gel



1607AirDS
Padded Divider Set



1607AirFS
3 pc. Replacement Foam Set

Peli

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999
info@peli.com • www.peli.com

Document created on 05-09-25